

HEYCO

Heyco-Flex™ Quick Twist Fittings with Assembled O-ring and Locknut




FITS HF1 CONDUIT TRADE SIZE	A Mounting Hole Diameter		PART NO. Gray	PART DIMENSIONS							
				B Max O.A. Length		C Body or Thread Length		D Wrenching Nut Thickness		E Wrenching Flats/Flange Dia.	
	in.	mm.		in.	mm.	in.	mm.	in.	mm.	in.	mm.
	Straight-Thru Style										
3/8	.875	22.2	8488RL	For Straight-Thru, NPT Hub Part Dimensions, see page 2-10							
1/2	.875	22.2	8494RL								
3/4	1.093	27.8	8498RL								

90° Sweep Style

3/8	.875	22,2	8503RL	For 90° Sweep, NPT Hub Part Dimensions, see page 2-14							
1/2	.875	22,2	8508RL								
3/4	1.093	27,8	8513RL								

Standard Color: Gray Fitting with Assembled Black O-Ring and Steel Locknut.



- O-Ring and steel locknut assembled for convenience and faster assembly.
- One-piece solution with smooth internal surfaces provides for easier wire routing, protection, and installation.
- Easy, permanent assembly: the installer twists the tubing over the connector ferrule.
- Fittings are for use with Heyco-Flex I Conduit. See page 2-1.
- All nylon construction is resistant to salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL certification and testing.)
- Suitable for a wide array of electrical applications:
 - Commercial and Industrial HVAC Systems
 - Motorized Equipment
 - Enclosed Power Sources
 - Garage Door Openers
 - Major Appliances
- If using a tapped hole, Teflon® tape is needed on the threads of the connector.
- Finishing collars available to neaten rough cut tubing ends. See page 2-9.
- **New! Assembly Tool available for assembling Quick Twist Fittings into HF1 and HF2 Conduit and Tubing.** See page 2-11.

Material	6/6 Nylon
Certifications	See and Listed File Numbers on pages 2-10 & 2-14
Flammability Rating	94V-2
Material Temperature Index	Maximum temperature on part not to exceed 221°F (105°C)

*Quick
Specs*