



Item no.: 739-166
Product description: PCB TERMINAL STRIP 1 SOLDER PIN / POLE 16 POLE PIN
SPACING 5.08 MM / 0.2 IN



Produkt kann von Bild abweichen / product may differ

Packing unit 40 4*10 pieces

RoHS compliant

Product group	4 (Printed Circuit)
Weight	19.08 g
Color	orange
No. of connection Points	16
No. of potentials	16
pole count	16
Height	15.8 mm
Height	0.622 in
Width	82.7 mm
Width	3.256 in
Depth	14.3 mm
Depth	0.563 in
Pin spacing from	5.08 mm
Pin spacing from	0.2 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	24 A
Pollution degree	2

Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	24 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm²]	0.08 - 2.5 mm²
Wiring method	solid
Cross section [mm²]	0.08 - 2.5 mm²
Cross section to [mm²]	1.5 mm²
Cross section to [mm²]	2.5 mm²
Cross section [AWG]	28 - 12 AWG
Strip length from	8 mm
Strip length to	9 mm
Material group	I



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
739-166	CCA	DK2079	250	12	0,5-2,5
739-166	CSA	154112-1711139	300	12	28-12
739-166	RMR	11130002	250	12	0,5-2,5
739-166	UR	E45172	300	12	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected