


PIN HEADER 2,54mm standard insulator

ID: 087


STL 1-XXXXG / STL 2-XXXXG / STL 3-XXXXG

Series 400



TECHNICAL DATA

Pitch	2,54 mm
Insulating Material	high temp. thermoplast UL94V-0
Contact Material	copper alloy
Rated Current	3 Amp.
Rated Voltage	250 V _{AC/DC}
Withstanding Voltage	1000 V _{AC} for one minute
Operating Temperature	-40°C to +105°C
Maximum Soldering Temperature	230°C for 30-60 seconds 260°C for 10 seconds



Code	Dimensions		
	A	B	C
1020	10,20	5,20	2,50
1080	10,80	5,80	2,50
1130	11,30	5,50	3,30
1260	12,60	6,80	3,30
1390	13,90	8,20	3,30
1470	14,70	9,00	3,30
1650	16,50	10,70	3,30
1770	17,70	12,10	3,30
1980	19,80	14,00	3,30
2160	21,60	15,80	3,30
2280	22,80	17,00	3,30
2490	24,90	19,10	3,30
Custom			

All dimensions in mm.
Other dimensions upon request.

STL X - XXXX G XX - XXX U

Rows: 1 = 1 rows
2 = 2 rows
3 = 3 rows

Code: see table

G: straight contacts

Plating: TT = Sn
GT = Sel. Au
GG = Au

U: RoHS-compliant with high temp. plastic

Pins: 1 row: 1 - 50 contacts
2 rows: 2 - 100 contacts
3 rows: 3 - 120 contacts