





TITLE	INDUCTOR, COMMON MODE	SCHOTT CORPORATION 1000 PARKERS LAKE ROAD WAYZATA, MN 55391	AGENCY APPROVAL:		PART NUMBER	
			N/A		REV O	PAGE 1 END

SPECIFICATIONS

- INDUCTANCE: @ 20 mVrms, 100 kHz
1-2 = 3.29 - 6.11 mH
- LEAKAGE INDUCTANCE: @ 20 mVrms, 100 kHz
1-2 tie 3&4 = 0.6 µH MAX
- DCR: 1-2 = 1 OHM MAX
4-3 = 1 OHM MAX
- HIPOT: 650 Vrms for 6 seconds, 1-4
- URNS RATIO: 1-2 : 4-3 = 1 : 1 ± 2%



NOTE:
COPLANARITY < .004 (0.10)



TOLERANCES	2 PLACE	3 PLACE	ANGLE
UNLESS OTHERWISE NOTED	± .01	± .005	± °