

Kegelsenker 90°
Countersink 90°



Art. 821

DIN 335 C, HSS, mit TIN (Titan-Nitrid) Beschichtung, mit Zylinderschaft und 3 Schneiden.

DIN 335 C, HSS, with TIN (titanium nitride) coating, with cylindrical shank and 3 Flutes.

CBN-tiefgeschliffen

CBN-deep-ground

- 2 383-337
b 383-417
c 383-594
d 383-620
e 383-612

Table with 11 columns: CODE, mm, DIN 74 Af, DIN 74 Bf, DIN 75 Af, DIN 75 Bf, mm, mm, mm, g, EURO, EAN-CODE. Rows include drill bit specifications and corresponding EAN codes.

Kegelsenker 90° in Stahlblechkassette
Countersink 90° in steel-plate cassette



Art. 821-620/650

DIN 335 C, HSS, mit TIN (Titan-Nitrid) Beschichtung, mit Zylinderschaft und 3 Schneiden.

DIN 335 C, HSS, with TIN (titanium nitride) coating, with cylindrical shank and 3 Flutes.

CBN-tiefgeschliffen

CBN-deep-ground

Table with 7 columns: CODE, No., Inhalt, g, EURO, EAN-CODE. Rows show cassette contents and weights.