


# 50W AC-DC Triple Output



- 3 pole AC inlet IEC320-C14
- Class I power (with earth pin)
- Protections: Short circuit / Overload / Over voltage
- Fully enclosed plastic case
- LED indicator for power on
- Approvals: UL / CUL / TUV / CB / CE
- 1 year warranty

AC input voltage range ..... 90~264VAC / 1.6A  
 AC inrush current(max.) .... Cold start, <40A at 230VAC  
 Overload protection ..... Hiccup mode, auto-recovery  
 Over voltage protection ..... 110~140% for +5V output  
 Hold up time ..... 12ms at full load  
 Withstand voltage ..... I/P-O/P:3KVAC, I/P-FG:1.5KVAC, 1 minute  
 Working temperature ..... 0~+40°C (refer to output load derating curve)  
 Safety standards ..... UL1950, TUV EN60950-1 approved  
 EMC standards ..... EN55022 class B, EN61000-3-2,3,  
 EN61000-4-2,3,4,5,6,11,  
 ENV50204  
 Length of output cable ..... 120cm of AWM 2464  
 Standard DC plug..... R1B: DIN 5P



| Stock No. | Order No.   | Output         | Tol. | R&N   | Effi. | Max. |
|-----------|-------------|----------------|------|-------|-------|------|
| 13701     | P50A13D-R1B | 5V, 0.5~4.0A   | ±6%  | 50mV  | 72%   | 50W  |
|           |             | 12V, 0.5~2.0A  | ±10% | 100mV |       |      |
|           |             | -12V, 0.1~0.5A | ±12% | 100mV |       |      |
| 13702     | P50A14E-R1B | 5V, 0.5~4.0A   | ±6%  | 50mV  | 74%   | 50W  |
|           |             | 15V, 0.5~1.5A  | ±10% | 100mV |       |      |
|           |             | -15V, 0.1~0.5A | ±12% | 100mV |       |      |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mean Well:](#)

[P50A13D-R1B](#)