



English | 简体中文 | 日本語

Search by Part Number

GO

Search Site by keyword

GO

Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Calculators | Cross Reference | Green Initiative | Military | Parametric Search | Search by Part Number, Keyword, Document, Green/Pb-Free, Package

Home > Products > > 813076 > 813076BYI-31LF

You may also like...

813076BYI-31LF

Category:

Generic Part: 813076

Market Group: NETCOM

Description: VCXO JITTER ATT AND FEMTO CLOCK

Time is money

Parameters

Speed	NA
Temperature	I
Voltage	3.3 V
Status	Active
Sample	Yes
Minimum Order Quantity	250
Factory Order Increment	250

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

No documents available for this part at this time.

Package

Package	PTQFP 48 (DXG48)
Description	TQFP 7 X7 X 1.0- EXPOSED PAD
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Mark	Y
Package Type	PTQFP
Lead Count	48
Length	7.0 mm
Width	7.0 mm
Thickness	1.0 mm
Pitch	0.5 mm
Tube / Tray	TRAY
Quantity per Tube/Tray	250
Quantity per Reel	1000
Moisture Sensitivity Level (MSL)	3
Moisture Exposure Floor Life	168hrs@<30C/60%RH
Peak Reflow Temperature	260Â°C
Rebake Conditions	48hrs@125C
Related Package Documents	view documents

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) [What is this?](#)

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. [All Rights Reserved](#).