

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVO
GP	00		P	REVISED PER ECO-11-004835	11MAR11	RK	HMR

.350 DIA MAX
CABLE OPENING

INTERNAL CABLE
TIE OPENINGS.

1.115 REF

1.312

EXTERNAL CABLE
TIE OPENINGS.

#4-40 HEX NUT STEEL
ZINC PLATED, 2 REQD
CLEAR CHROMATE COATED

#4-40 CRS SCREW,
ZINC PLATED, 2 REQD
CLEAR CHROMATE COATING

1.750 REF

AMP

1.550 ±.010

TWO PIECE CABLE
SUPPORT HOUSING
MATERIAL:
THERMOPLASTIC, GRAY

#4-40 CRS SCREW,
ZINC PLATED, 2 REQD
YELLOW CHROMATE COATED

.500 ±.010


.620 REF

1. THIS PART WILL FIT ANY STANDARD SIZE 2 PLUG OR
RECEPTACLE IN THE AMPLIMITE SERIES.

2. ALL PARTS ARE PACKAGED UNASSEMBLED.

5206471-1

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.RICHARDSON	31AUG05	 TE Connectivity			
DIMENSIONS: INCHES		CHK C.ROHDE	31AUG05				
		APVD M.WALMSLEY	31AUG05	NAME			
		PRODUCT SPEC		CABLE CLAMP ASSEMBLY, SIZE 2, 15 POSITION, AMPLIMITE HD-20			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -		—		A2	00779	C=5206471	—
1 PLC ± -		—		SCALE 4:1			
2 PLC ± -		—		SHEET 1 OF 1			
3 PLC ± .005		—		REV P			
4 PLC ± -		—					
ANGLES ± -		—					
FINISH		WEIGHT					
SEE CALLOUTS		—					
SEE CALLOUTS		CUSTOMER DRAWING					