


Plug


171-0129-EX

KOBI CONN


Plug



Front View



Side View



Rear View

Dimensions: In.

SPECIFICATIONS	
Type:	auto power
Rating:	12VDC 3A
Contact resistance:	100mΩ max.
Insulation resistance:	50MΩ min. @ 250VDC
Breakdown voltage:	250VAC for 1 minute
Body, cap:	ABS, black
Sleeve contact:	nickel plated steel
Tip contact:	nickel plated brass
Tip terminal:	brass
Tip spring:	piano wire
RoHS Compliant by Exemption	

171-0129-EX

Date Last Revised: 12-21-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300904

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-0129-EX](#)