





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
J	—	P	LTR	DESCRIPTION	DATE DWN APVD
		E1	REVISED	ECR-06-003257	10FEB06 TS KB

プリント基板取付穴寸法 公差 ± 0.1
 (MOUNTING DIMENSIONS FOR P.C.B. ; TOLERANCES ± 0.1)




- △ -T- 面より2mmの範囲で測定
 2. 適合する相手ハウジング型番は172245, 172854
 3. 適用製品規格 NO. 108-5124
 △ 推奨取付ねじ ; JIS B1115, B1122 タッピンねじ
 なべ3種 呼び径2, 長さ5

- △ THESE DIMENSIONS TO BE MESURED BETWEEN -T- AND 2.0.
 2. MATABLE PLUG HOUSING ; 172245, 172854
 3. PRODUCT SPECIFICATION ; 108-5124
 △ RECOMMENDED MOUNTING SCREW ; JIS B1115 OR B1122
 PAN HEAD TAPPING SCREW, CLASS 3, DIAMETER 2, LENGTH 5.

SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT)	BLACK	172259-4
SELECTIVE-TIN	PRE-TIN	BLACK	172259-2
SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
CONTACT FINISH コンタクト仕上			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 概
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL
材料
HOUSING ; 66NYLON
CONTACT ; COPPER ALLOY

FINISH
仕上

SEE TABLE

DWN	T.SHINOHAR	10FEB06
CHK	K.BETSUI	10FEB06
APVD	K.BETSUI	10FEB06
PRODUCT SPEC	SEE NOTE 3	
APPLICATION SPEC	取付適用規格	
WEIGHT	—	

CUSTOMER DRAWING

tyco Electronics		Tyco Electronics AMP K.K. Kawasaki, Japan	
NAME 名称			
12POSITION VERTICALTYPE CAP HOUSING ASSEMBLY DUALLINE INTERLOCK CONNECTOR			
SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-172259	—
SCALE 尺度 2:1		SHEET 1 OF 1	REV E1

一般公差 (GENERAL TOLERANCE)	
10以下	±0.2
10を超え 30以下	±0.25
30を超え 100以下	±0.3
角 度	±3°