

## Stubby Augers

Single flute design for  
cleaner holes

Fast and smooth  
cutting action



5/8"

3/4"

7/8"

1"

## ***Small Auger Packs a Big Punch!***

Greenlee is proud to add Greenlee's Stubby Auger Bits to the Holemaking Product Category. The new Stubby Auger Bits were designed so that it's easier to drill a hole in tight spaces such as between studs, joists and inside walls. With the new stubby auger bits, there's no longer a need for expensive right angle drills or multiple steps in order to cut holes to size.

The unique cutting design provides fast and smooth cutting action. The 1/4" hex quick change design allows for fast

and easy use in all ranges of drill types. Both the 5/8" and 3/4" stubby bits can be used with Greenlee's New Quick Connect Extensions.

The new Stubby Auger Bits are yet another way that Greenlee helps to make your job faster, safer, and easier.

## Features

- Over center single flute design for cleaner holes and less splintering.
- Unique cutting edge design for fast and smooth cutting action.
- Shorter than the top competitor's bit for better access to tight spaces between studs and joists.
- Perfect for drilling 2" and 4" joists.
- Self-Feeding screw point draws bit through all wood types with less operator fatigue.
- Eliminates the need for special tools such as expensive right angle drills or multiple steps to cut the hole to size.
- 1/4" hex quick change design for fast and easy use in all drill types.
- Clearly marked with bit diameter and catalog number on shank for easy identification.

## Capacity

- Maximum bit capacity for Quick Connect Extensions is 3/4".
- Not for use in wood with nails.

## Specifications

| CAT#    | UPC#  | Description           | Hole Diameter<br>Inch (mm) | Overall Length<br>Inch (mm) | Weight<br>Lbs. (g) |
|---------|-------|-----------------------|----------------------------|-----------------------------|--------------------|
| 60A-5/8 | 12416 | 5/8" Stubby Auger Bit | 5/8" (15.9mm)              | 4.5" (114mm)                | .3 lbs. (118g)     |
| 60A-3/4 | 12417 | 3/4" Stubby Auger Bit | 3/4" (19.1mm)              | 4.5" (114mm)                | .3 lbs. (136g)     |
| 60A-7/8 | 12418 | 7/8" Stubby Auger Bit | 7/8" (22.2mm)              | 4.5" (114mm)                | .3 lbs. (149g)     |
| 60A-1   | 10538 | 1" Stubby Auger Bit   | 1" (25.4mm)                | 4.5" (114mm)                | .4 lbs. (199g)     |

## Ordering Information

| Cat#    | UPC#  | Description           | Qty |
|---------|-------|-----------------------|-----|
| 60A-5/8 | 12416 | 5/8" Stubby Auger Bit | 1   |
| 60A-3/4 | 12417 | 3/4" Stubby Auger Bit | 1   |
| 60A-7/8 | 12418 | 7/8" Stubby Auger Bit | 1   |
| 60A-1   | 10538 | 1" Stubby Auger Bit   | 1   |

### DISTRIBUTOR INFORMATION :



**USA** Tel: 800.435.0786  
Fax: 800.451.2632

**Canada** Tel: 800.435.0786  
Fax: 800.524.2853

**International** Tel: +1.815.397.7070  
Fax: +1.815.397.9247