


CR1216


■ Dimensions(mm)




■ Specification

Nominal voltage(V)	3
Nominal capacity(mAh)	25
Continuous drain(mA)	0.1
Operating temperature(°C)	-30 to +60


■ Discharge temperature characteristics



■ Operating voltage vs. load resistance(voltage at 50% discharge depth)




■ Capacity vs. load resistance



CR1220


■ Dimensions(mm)




■ Specification

Nominal voltage(V)	3
Nominal capacity(mAh)	35
Continuous drain(mA)	0.1
Operating temperature(°C)	-30 to +60

■ Discharge temperature characteristics



■ Operating voltage vs. load resistance(voltage at 50% discharge depth)



■ Capacity vs. load resistance

