


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191600042](#)
Status: **Active**
Description: Twist Lock Splice for 10-22 AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Splices
Series	19160
Mil-Spec	N/A
Product Name	Closed-End Twist Lock
Physical	
Barrel Type	Closed
Flammability	94V-2
Insulation	Nylon (PA)
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	11.2mm (.44") max
Wire Size AWG	10, 12, 14, 16, 18, 20, 22, 24, 26
Wire Size mm²	0.25 - 6.60
Electrical	
CSA	700095
UL	E32244
Voltage - Maximum	600V
Material Info	
Old Part Number	TL-Y
Reference - Drawing Numbers	
Sales Drawing	SD-19160-005



*Series
image - Reference only*

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19160Series](#)