

Panel mounting base - HC-MOD-K-AFS-OPE - 1408559

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plastic panel mounting base for modules for a module slot, without PE marking, for snap locking

Key commercial data

Packing unit	0
Minimum order quantity	2
Catalog page	Page 555 (PC-2011)
GTIN	 4 046356 619295
Custom tariff number	85389099
Country of origin	GERMANY

Technical data

General data

Height	22.4 mm
Width	21.8 mm
Length	54 mm
Color	light gray
Locking type	for snap locking
Screw connection	None
Degree of protection for housing	IP65 protection when the connector is inserted
Ambient temperature (operation)	-40 °C ... 85 °C
Housing material	polycarbonate
Inflammability class according to UL 94	V0
Length of the assembly cutout	37 mm
Width of the assembly cutout	18 mm
Assembly instructions	up to 50 V (missing PE)

Classifications

eclass

eCl@ss 4.0	23090101
eCl@ss 4.1	23090101

Panel mounting base - HC-MOD-K-AFS-OPE - 1408559

Classifications

eclass

eCl@ss 5.0	23090101
eCl@ss 5.1	23090101
eCl@ss 6.0	23090101
eCl@ss 7.0	23090101

etim

ETIM 4.0	EC000437
----------	----------

unspsc

UNSPSC 6.01	31161807
UNSPSC 7.0901	31161807
UNSPSC 11	31161807
UNSPSC 12.01	31161807
UNSPSC 13.2	31161807

Accessories

Accessories


Coding profile - HC-MOD-K-CP - 1408562



Coding profile for HC-MOD-K... housing

Drawings

Dimensioned drawing



Dimensional drawing