




## Introducing SBPlus Self Laminating Wire and Cable Markers

# SBPlus Self Laminating Wire and Cable Markers

## KEY FEATURES

- More aggressive adhesive than the current SB product it replaces.
- Adhesive helps to prevent lift off in the most demanding applications.
- Clear base material allows the printing to remain more legible after over-lamination.

## DESCRIPTIONS

Clear vinyl film with a permanent acrylic based adhesive, supplied with a white thermal transfer printable area, which is over-laminated upon application with the clear portion of the label.

## APPLICATIONS

Used to identify commercial and industrial grade wire and cable products with an operating temperature range of -51C to +93C (-60F to +200F)

## MECHANICAL

Clear over-lamination provides mechanical and splash fluid protection to the printed area of the label.

## MATERIALS

Clear vinyl with a thermal transfer printable white area for printing.

## PRODUCT OFFERING

Packaged on both 1” and 3” diameter cores. Quantity per package ranges from 10,000 labels per spool for the smallest sizes to 1,000 labels per spool for the largest sizes.

## APPLICATION TOOLING

No special application tooling is required. Print using a qualified Tyco Electronics Thermal Transfer printer and ribbon.

## PRODUCT INFORMATION



Available Sizes and Formats

| Printer Model | Approved Ribbon       | Certification |
|---------------|-----------------------|---------------|
| T208M         | TMS-101-RIBBON-4RPSCE | UL 969        |
| T212M         | TMS-101-RIBBON-4RPSCE | UL 969        |
| T308S         | TMS-RJS-RIBBON-4RPSCE | UL 969        |
| T312S         | TMS-RJS-RIBBON-4RPSCE | UL 969        |
| TE3012M       | TMS-RJS-RIBBON-4RPSCE | UL 969        |
| TE3112M       | TMS-RJS-RIBBON-4RPSCE | UL 969        |
| TE3124M       | TMS-RJS-RIBBON-4RPSCE | UL 969        |



## SBPlus Self Laminating Wire and Cable Markers

### Part Numbering System



### Available Sizes and Formats

| Ordering Description | Package Quantity | Labels Across | Max Cable OD |        | (A) Label Width |        | (B) Label Height |        | (C) Printable Height |        | (D) Horizontal Repeat |        | (E) Vertical Repeat |        | (F) Web Width |        |
|----------------------|------------------|---------------|--------------|--------|-----------------|--------|------------------|--------|----------------------|--------|-----------------------|--------|---------------------|--------|---------------|--------|
|                      |                  |               | mm           | inches | mm              | inches | mm               | inches | mm                   | inches | mm                    | inches | mm                  | inches | mm            | inches |
| SBP050100WE10        | 10,000           | 5             | 5.1          | .20    | 12.70           | 0.500  | 25.40            | 1.000  | 8.50                 | 0.330  | 16.80                 | 0.600  | 31.00               | 1.222  | 86.00         | 3.384  |
| SBP050143WE10        | 10,000           | 5             | 7.6          | .30    | 2.70            | 0.500  | 36.50            | 1.437  | 12.70                | 0.500  | 16.80                 | 0.662  | 42.20               | 1.661  | 86.00         | 3.384  |
| SBP075094WE10        | 10,000           | 4             | 7.6          | .30    | 19.10           | 0.750  | 23.90            | 0.940  | 9.50                 | 0.375  | 20.30                 | 0.800  | 28.60               | 1.125  | 85.10         | 3.350  |
| SBP080150WE10        | 10,000           | 4             | 7.6          | .30    | 20.30           | 0.800  | 38.10            | 1.500  | 12.70                | 0.500  | 22.90                 | 0.900  | 44.50               | 1.750  | 94.90         | 3.736  |
| SBP100143WE5         | 5,000            | 3             | 7.6          | .30    | 25.40           | 1.000  | 36.50            | 1.437  | 12.70                | 0.500  | 27.90                 | 1.100  | 42.20               | 1.661  | 87.30         | 3.436  |
| SBP100225WE5         | 5,000            | 3             | 12.2         | .48    | 25.40           | 1.000  | 57.20            | 2.250  | 19.10                | 0.750  | 27.90                 | 1.100  | 66.70               | 2.625  | 87.30         | 3.436  |
| SBP100375WE2.5       | 2,500            | 3             | 22.4         | .88    | 25.40           | 1.000  | 95.30            | 3.750  | 25.40                | 1.000  | 27.90                 | 1.100  | 101.60              | 4.000  | 87.30         | 3.436  |
| SBPH100375WE2.5      | 2,500            | 1*            | 22.4         | .88    | 25.40           | 1.000  | 95.30            | 3.750  | 25.40                | 1.000  | N/A                   | N/A    | 28.60               | 1.125  | 100.30        | 3.950  |
| SBP100594WE1         | 1,000            | 3             | 35.6         | 1.4    | 25.4            | 1.000  | 151.00           | 5.940  | 38.10                | 1.500  | 27.90                 | 1.100  | 158.80              | 6.250  | 87.30         | 3.436  |
| SBP100743WE1         | 1,000            | 3             | 35.6         | 1.4    | 25.40           | 1.000  | 188.90           | 7.437  | 38.10                | 1.500  | 27.90                 | 1.100  | 195.30              | 7.688  | 87.30         | 3.436  |
| SBP190319WE2.5       | 2,500            | 2             | 12.2         | .48    | 48.30           | 1.900  | 81.00            | 3.190  | 19.10                | 0.750  | 50.80                 | 2.000  | 87.40               | 3.440  | 105.10        | 4.138  |
| SBP190594WE1         | 1,000            | 2             | 35.6         | 1.4    | 48.30           | 1.900  | 151.00           | 5.940  | 38.10                | 1.500  | 50.80                 | 2.000  | 158.80              | 6.250  | 105.10        | 4.138  |
| SBP200143WE2.5       | 2,500            | 2             | 7.6          | .30    | 50.80           | 2.000  | 6.50             | 1.437  | 12.70                | 0.500  | 50.80                 | 2.000  | 42.20               | 1.661  | 107.60        | 4.236  |
| SBP200225WE2.5       | 2,500            | 2             | 12.2         | .48    | 50.80           | 2.000  | 57.20            | 2.250  | 19.10                | 0.750  | 50.80                 | 2.000  | 66.70               | 2.625  | 107.60        | 4.236  |
| SBP200375WE2.5       | 2,500            | 2             | 22.4         | .88    | 50.80           | 2.000  | 95.30            | 3.750  | 25.40                | 1.000  | 53.30                 | 2.100  | 101.60              | 4.000  | 111.40        | 4.386  |
| SBP200743WE          | 11,000           | 2             | 48.3         | 1.9    | 50.80           | 2.000  | 188.90           | 7.437  | 38.10                | 1.500  | 53.30                 | 2.100  | 195.30              | 7.688  | 110.10        | 4.336  |

\*One label across rotated format.

### Options

|        |              |                                                         |
|--------|--------------|---------------------------------------------------------|
| Colors | Standard     | White with clear tail                                   |
|        | Non-Standard | Red, Orange, Yellow, Green, Blue, Violet and Clear Tail |

## FOR MORE INFORMATION

### Technical Support

|                |                                                                                      |
|----------------|--------------------------------------------------------------------------------------|
| Internet:      | <a href="http://www.tycoelectronics.com">www.tycoelectronics.com</a>                 |
| E-mail:        | <a href="mailto:newproducts@tycoelectronics.com">newproducts@tycoelectronics.com</a> |
| USA:           | 1-800-522-6752                                                                       |
| Canada:        | 1-905-470-4425                                                                       |
| Mexico:        | 1-800-733-8926                                                                       |
| C. America:    | 52-55-1106-0803                                                                      |
| South America: | 55-11-2103-6000                                                                      |
| Hong Kong:     | 852-2735-1628                                                                        |
| Japan:         | 81-44-844-8013                                                                       |
| UK:            | 44-8706-080208                                                                       |

**Tyco Electronics Corporation**  
Harrisburg, PA

**[tycoelectronics.com](http://tycoelectronics.com)**

Copyright 2008 Tyco Electronics Corporation  
6-1773453-1 2.5M FP 12/2008  
TE logo and Tyco Electronics are trademarks.

