

Router - FL MGUARD PCI/266 - 2989019

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Firewall/router in PCI format 266 MHz processor cycle frequency

RoHS

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	117.500 g
Custom tariff number	85176200
Country of origin	Germany

Technical data

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	0 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 % (non-condensing)

Interfaces

Interface	Ethernet
No. of ports	2
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 Mbps
Signal LEDs	WAN link, WAN activity, LAN link, LAN activity

Function

Basic functions	Firewall/Router
Supported browsers	HTTPS support required
Processor	266 MHz
Status and diagnostic indicators	Link/activity per port

Router - FL MGUARD PCI/266 - 2989019

Technical data

Network expansion parameters

Maximum conductor length (twisted pair)	100 m
---	-------

General

Mounting type	PCI slot
Net weight	117.5 g

Security functions

Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Network Time Protocol (NTP) client	Client
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Remote Syslog Logging	On external server
Virtual private network (VPN) throughput	max. 85 Mbps (Router mode, VPN bidirectional throughput)
	max. 58 Mbps (Stealth mode, VPN bidirectional throughput)
Encryption methods	DES, 3DES, AES-128, -192, -256
Firewall data throughput	max. 210 Mbps (Router mode, default firewall rules, bidirectional throughput)
	max. 149 Mbps (Stealth mode, default firewall rules, bidirectional throughput)
Firewall rules	Configurable stateful inspection firewall
Filtering	MAC and IP addresses, ports, protocols
Protection against	IP spoofing, DoS and Syn Flood Protection
Routing	NAT, 1:1-NAT, Port Forwarding

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
-------------------------------	--

Classifications

eCl@ss

eCl@ss 4.0	27240409
eCl@ss 4.1	27240409
eCl@ss 5.0	27242215
eCl@ss 5.1	19030101
eCl@ss 6.0	27242208

ETIM

ETIM 2.0	EC001423
ETIM 3.0	EC001423
ETIM 4.0	EC001423

Router - FL MGUARD PCI/266 - 2989019

Classifications

UNSPSC

UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601
UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	20142601

Accessories

Accessories

License

License - FL MGUARD LIC LIFETIME FW - 2700184



License for lifetime software update of FL MGUARD field devices.

License - FL MGUARD LIC CIM - 2701083



License for activating CIFS Integrity Monitoring (CIM) on an FL MGUARD

License - FL MGUARD LIC VPN-250 GROUP - 2700192



License for up to 250 additional VPN online connections

Router - FL MGUARD PCI/266 - 2989019

Accessories

License - FL MGUARD LIC VPN-250 - 2700193



License for up to 250 additional VPN online connections

License - FL MGUARD LIC VPN-10 - 2700194



License for up to 10 additional VPN online connections

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250



Patch cable, CAT5, assembled, 0.3 m

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1 m

Router - FL MGUARD PCI/266 - 2989019

Accessories

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2 m

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3 m

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5 m

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

Router - FL MGUARD PCI/266 - 2989019

Accessories

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10 m

Patch cable - FL CAT6 PATCH 12,5 - 2891369



Patch cable, CAT6, pre-assembled, 12.5 m

Patch cable - FL CAT6 PATCH 15,0 - 2891372



Patch cable, CAT6, pre-assembled, 15.0 m

Patch cable - FL CAT6 PATCH 20,0 - 2891576



Patch cable, CAT6, pre-assembled, 20.0 m

Plug

RJ45 connector - FL PLUG RJ45 GR/2 - 2744856



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve.

Router - FL MGUARD PCI/266 - 2989019

Accessories

RJ45 connector - FL PLUG RJ45 GN/2 - 2744571



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.

Protective cap

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

Assembly tool - FL CRIMPTOOL - 2744869



Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site