








7. SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.
6. MATERIAL - HOUSING: PLASTIC; GROMMET: RUBBER.
5. THIS PLUG MATES WITH DTM04-12P*-**** RECEPTACLE.
(* = A,B,C,D KEYS; **** = ALL MODIFICATIONS)
4. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.
3. SECONDARY WEDGE LOCK SOLD SEPARATELY: WM-12S.
2. DIMENSION TOLERANCE: $\pm .025$ [.64].
1. DIMENSIONS ARE IN INCHES [mm].

NOTES: UNLESS OTHERWISE SPECIFIED

REV
NC

DTM06-12S*

REVISIONS

SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. P17240	4-19-01	RDR

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-22 AWG [1.0-0.5]


SIGNATURE & DATE	
DR	J. APOSTOL 17 APR 2001
CHK	R. Rader 4/18/01
PE	D. Meyer 4/17/01
APPD	R. Rader 4-19-01
SCALE	NONE
WT	

PLUG
12 CONTACTS, SIZE 20
A,B,C,D KEYS
DTM SERIES


ENVELOPE

CP	MATL. CODE
The Deutsch Company DEUTSCH I.P.D. 3850 INDUSTRIAL AVE. HEMET, CALIF. 92545	
B	DTM06-12S*
DWG SIZE	CODE 11139
SHEET 1 OF 2	


REV NC		DTM06-12S*		REVISIONS			
SYM		DESCRIPTION		DATE	APPROVED		
		SEE SHEET ONE		4-19-01	RDR		




DTM06-12SA
KEY -A-
COLOR: GREY




DTM06-12SB
KEY -B-
COLOR: BLACK




DTM06-12SC
KEY -C-
COLOR: GREEN




DTM06-12SD
KEY -D-
COLOR: BROWN




DTM06-12SA
KEY -A-
COLOR: GREY



DTM06-12SB
KEY -B-
COLOR: BLACK



DTM06-12SC
KEY -C-
COLOR: GREEN



DTM06-12SD
KEY -D-
COLOR: BROWN

SIGNATURE & DATE	
DR	J. APOSTOL 17APR2001
CHK	Rmly 4/18/01
PE	Dmex 4/17/01
APPD	
SCALE	NONE WT

PLUG
12 CONTACTS, SIZE 20
A,B,C,D KEYS
DTM SERIES

ENVELOPE

CP	MATL. CODE
The Deutsch Company DEUTSCH I.P.D. 3850 INDUSTRIAL AVE. HEMET, CALIF. 92545	
B	DTM06-12S*
DWG SIZE	CODE 11139 SHEET 2 OF 2

NOTES: