







Recommended PCB Layout
(Bottom View)

Material and Finish

Inner Shield: copper alloy,
tin plated

Outer Shield: steel, tin plated

Body: PBT thermoplastic
UL94V-0 rated
color - black

Contacts: brass, tin plated


Electrical Characteristics

Contact Rating:
7.5A max. @ 20V DC

Insulation Resistance:
50 Megohms min. at 250V DC

Dielectric Strength:
250 V AC rms for 1 minute

Contact Resistance:
50 milliohms max.



Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise

REVISION	DATE	DESCRIPTION	DRAWN BY	CHECKED BY	UNITS
A5	12/13/00	Ref ECD 00-213	C. Leiva	H. MA	mm
A6	7/09/01	Ref ECD 01-085	REVISED BY	CHECK DATE	DATE
A7	12/03/02	Ref ECD 02-136	T. Gokcek	12/04/02	3/4/98

KPJ-4S-S

DC Power Jack

4 position, Shielded



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KPJ-4S-S](#)