



TLS 2200®/TLS PC Link™ Labels

TLS 2200®/TLS PC Link™ Label Index By Size (Continued)

Diagram	Catalog Number	Labels Per Roll	Material	Color	B-Number	Label Width Inch (mm) A	Label Height Inch (mm) B	Write-On Height Inch (mm) C	Wire Gauge
0.500" (Continued)									
Fig. 6	PTL-11-499	500	Nylon	White	B-499	0.500 (12.7)	0.750 (19.1)	—	16 to 10
Fig. 6	BPTL-11-499	5000	Nylon	White	B-499	0.500 (12.7)	0.750 (19.1)	—	16 to 10
Fig. 6	PTL-11-498	500	Vinyl	White	B-498	0.500 (12.7)	0.750 (19.1)	—	16 to 10
Fig. 6	BPTL-11-498	5000	Vinyl	White	B-498	0.500 (12.7)	0.750 (19.1)	—	16 to 10
Fig. 7	PTL-11-427	500	Vinyl	White	B-427	0.500 (12.7)	0.750 (19.1)	0.375 (9.5)	16 to 10
Fig. 7	BPTL-11-427	5000	Vinyl	White	B-427	0.500 (12.7)	0.750 (19.1)	0.375 (9.5)	16 to 10
Fig. 7	PTL-11-427-YL	500	Vinyl	Yellow	B-427	0.500 (12.7)	0.750 (19.1)	0.375 (9.5)	16 to 10
Fig. 7	PTL-17-427	500	Vinyl	White	B-427	0.500 (12.7)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	BPTL-17-427	5000	Vinyl	White	B-427	0.500 (12.7)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-17-427-YL	500	Vinyl	Yellow	B-427	0.500 (12.7)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-102-427	250	Vinyl	White	B-427	0.500 (12.7)	1.250 (31.8)	0.375 (9.5)	10 to 4
Fig. 6	PTL-29-499	500	Nylon	White	B-499	0.500 (12.7)	1.500 (38.1)	—	10 to 4
Fig. 6	PTL-29-498	500	Nylon	White	B-499	0.500 (12.7)	1.500 (38.1)	—	10 to 4
Fig. 6	BPTL-29-498	5000	Vinyl	White	B-498	0.500 (12.7)	1.500 (38.1)	—	10 to 4
Fig. 7	PTL-29-427	500	Vinyl	White	B-427	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	BPTL-29-427	5000	Vinyl	White	B-427	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-29-427-BL	500	Vinyl	Blue	B-427	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-29-427-BR	500	Vinyl	Brown	B-427	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-29-427-GR	500	Vinyl	Green	B-427	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-29-427-GY	500	Vinyl	Gray	B-427	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-29-427-OR	500	Vinyl	Orange	B-427	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-29-427-RD	500	Vinyl	Red	B-427	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-29-427-YL	500	Vinyl	Yellow	B-427	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-29-427-PL	500	Vinyl	Purple	B-427	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 2	PTL-72-461	500	Polyester	White	B-461	0.500 (12.7)	1.800 (45.7)	0.500 (12.7)	—
Fig. 2	PTL-74-461	100	Polyester	White	B-461	0.500 (12.7)	2.200 (55.8)	0.750 (19.1)	—
Fig. 2	PTL-74-427	100	Vinyl	White	B-427	0.500 (12.7)	2.200 (55.8)	0.750 (19.1)	—
Fig. 8	PTL-8-498	Continuous	Polyvinylfluoride	White	B-437	0.500 (12.7)	30 ft. (9.1 m)	—	—
Fig. 8	PTL-8-422	Continuous	Polyester	White	B-422	0.500 (12.7)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-8-423	Continuous	Polyester	White	B-423	0.500 (12.7)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-8-428	Continuous	Polyester	Silver	B-428	0.500 (12.7)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-8-430	Continuous	Polyester	Clear	B-430	0.500 (12.7)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-8-432	Continuous	Polyester	Clear	B-432	0.500 (12.7)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-8-439	Continuous	Vinyl	White	B-439	0.500 (12.7)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-8-439-BK	Continuous	Vinyl	Black	B-439	0.500 (12.7)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-8-439-BL	Continuous	Vinyl	Blue	B-439	0.500 (12.7)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-8-439-GR	Continuous	Vinyl	Green	B-439	0.500 (12.7)	50 ft. (15.2 m)	—	—

