

## Straight Blade Devices

**60 Ampere, 125/250 Volts, 3Ø 250 and 120/208 Volts AC**


3 Pole, 4 Wire Grounding and 4 Pole, 4 Wire Non-Grounding

**Single Receptacles and Plugs****60A, 125/250V****3 Pole, 4 Wire Grounding  
Receptacles and Plugs****IP20**  
SUITABILITY**60A 125/250V**  
NEMA 14-60R  
UL CSA  
3(2) HP**60A 125/250V**  
NEMA 14-60P  
UL CSA  
3(2) HP


| Description                     | Cord Diameter                 | Catalog Numbers |                 |
|---------------------------------|-------------------------------|-----------------|-----------------|
| Receptacle, black RTP.          | —                             | <b>HBL9460A</b> | —               |
| Plug, nylon.                    | .625" - 1.310"<br>(15.9-33.3) | —               | <b>HBL9461C</b> |
| Plug, nylon, angle, 4-position. | .625" - 1.310"<br>(15.9-33.3) | —               | <b>HBL9462C</b> |

**HBL9461C****60A, 3Ø 250V AC****3 Pole, 4 Wire Grounding  
Receptacles and Plugs****IP20**  
SUITABILITY**60A 3Ø 250V AC**  
NEMA 15-60R  
UL CSA  
10 HP**60A 3Ø 250V AC**  
NEMA 15-60P  
UL CSA  
10 HP

| Description                     | Cord Diameter                 | Catalog Numbers |                 |
|---------------------------------|-------------------------------|-----------------|-----------------|
| Receptacle, black RTP.          | —                             | <b>HBL8460A</b> | —               |
| Plug, nylon.                    | .625" - 1.310"<br>(15.9-33.3) | —               | <b>HBL8461C</b> |
| Plug, nylon, angle, 4-position. | .625" - 1.310"<br>(15.9-33.3) | —               | <b>HBL8462C</b> |

**HBL8462C****60A, 3ØY 120/208V AC****4 Pole, 4 Wire Non-Grounding  
Receptacles and Plugs****IP20**  
SUITABILITY**60A 3ØY**  
**120/208V AC**  
NEMA 18-60R  
UL Listed  
7.5 HP**60A 3ØY**  
**120/208V AC**  
NEMA 18-60P  
UL Listed  
7.5 HP

| Description                     | Cord Diameter                 | Catalog Numbers |                 |
|---------------------------------|-------------------------------|-----------------|-----------------|
| Receptacle, black RTP.          | —                             | <b>HBL7301A</b> | —               |
| Plug, nylon.                    | .625" - 1.310"<br>(15.9-33.3) | —               | <b>HBL7303C</b> |
| Plug, nylon, angle, 4-position. | .625" - 1.310"<br>(15.9-33.3) | —               | <b>HBL7302C</b> |

**HBL7301A**

Note: See page A-47 for accessories.

RTP is an abbreviation for reinforced thermoplastic polyester.