


DESCRIPTION: HIGH DENSITY VERTICAL HIGH PROFILE STAMPED



MATERIALS:

INSULATOR: PBT, UL94V-0, 230°C PROCESS TEMP.
CHEMICAL RESISTANCE, COLOR BLACK

SHELL: STEEL, NICKEL PLATED

CONTACT: FEMALE: PHOSPHOR BRONZE
GOLD FLASH IN MATING AREA
TIN PLATING ON TAIL ENDS

RoHS COMPLIANT

ELECTRICAL:

CURRENT RATING: 2 AMPERES
DIELECTRIC WITHSTANDING VOLTAGE:
1000VAC rms AT SEA LEVEL
INSULATION RESISTANCE: 5000 MEGOHMS MIN.
CONTACT RESISTANCE: 10 MILLIOHMS MAX.
WORKING TEMPERATURE: -55° TO +125° C

198-XXX-213LXX1


SERIES _____
NUMBER OF CONTACTS _____
GENDER _____
2 = FEMALE (NO GROUND INDENTS)
(FEMALE ONLY)
PC MOUNT _____
3 = NICKEL SHELL _____
HARDWARE OPTIONS: _____
00 = .120" MOUNTING HOLE
55 = 4-40 INSERTS
03 = 4-40 HEX STANDOFFS
PLATING: _____
1 = GOLD FLASH

NUMBER OF CONTACTS	"A" Inch (mm)	"B" Inch (mm)	"C" Inch (mm)	"D" Inch (mm)
15	1.214 (30.84)	.984 (24.99)	.405 (10.29)	.090 (2.29)
26	1.545 (39.24)	1.312 (33.32)	.765 (19.43)	.090 (2.29)


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 9-15-05	
		CHECKED:		DATE:	
		SCALE:	SHEET 1 OF 1		REV 1
		DWG NO. 198-XXX-213LXX1			

DESCRIPTION: HIGH DENSITY DIP SOLDER FEMALE FOOTPRINT


78 POSITION FEMALE




26 POSITION FEMALE




62 POSITION FEMALE



15 POSITION FEMALE



44 POSITION FEMALE



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN:
PAM JENKINS

DATE:
10-29-01

CHECKED:

DATE:

SCALE:

SHEET 1 OF 1

REV 4

DWG NO.
HIGH DENSITY VERTICAL FEMALE FOOTPRINT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[198-015-213L031](#) [198-015-213L001](#) [198-026-213L001](#)