



T&B® Fittings

T&B Catalog Number: LT125P
UPC Number: 78621045068
Description: 1 1/4" Non-Metallic liquidtight Bullet®; -Straight. For use with liquidtight non-metallic Type B conduit or liquidtight non-metallic tubing.
Status: Active

WEB_USE

-T&B Product Line 012

Features

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.

Application

- The Bullet®; meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.

General

-Trade Size (inches) 1 1/4
 -Material Thermoplastic

Dimension Information

-Dimension A (inches) 0.750
 -Dimension B (inches) 2.164
 -Dimension C (inches) 2.494
 -Dimension D-Minimum Throat (inches) 1.257
 -E- NPT Thread (inches) 1 1/4-11 1/2
 -A (mm) 19.05
 -B (mm) 54.97
 -C (mm) 63.35
 -D (mm) 31.93
 -Dimension A (inches) 0.750
 -Dimension B (inches) 2.164
 -Dimension C (inches) 2.494

Specifications

-3dmodel Available on Website

Packaging

-T&B Inner Pack 5
 -Package in Units 25
 -T&B Sold in UOM Each
 -T&B Weight Per UOM 33.8 lbs. per 100

Application Support

-T&B Instruction Sheets ta00998-tb2
 -Guide to Nonmetallic Conduit Applications Available on Website
 -XTRAFLEX System Specifications Available on Website

-*Note

Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

-RoHS Compliance

Yes



File Nbr:

E 23018

For further technical assistance, please contact us...

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com