


HGP Series



- HGP-05AM
- HGP-12AM
- HGP-12AM-A3.2

- Pb (lead) free RoHS compliant
- High SPL



Specifications:

	HGP-05AM	HGP-12AM(-A3.2)
SPL	Min. 85 dB Typ. 90 dB	
Rated Voltage	5 V _{p-p}	12 V _{p-p}
Rated Frequency	2000 Hz	
Current Consumption	Mean: max 70 mA Peak: max 200 mA	Mean: max 50mA Peak: max 150 mA
Operation Temp.	-40°C to +90°C	
External Size	φ16mm x 12mm	
Mass	4 g	

Note: HGP-12AM-A3.2 has 3.2mm long pins

