

PRODUCT NUMBER	NUMBER OF POS.	DIM"C"	DIM"D"
95290-Y03(Z)LF	2 x 03	5.08	7.54
95290-Y04(Z)LF	2 x 04	7.62	10.08
95290-Y05(Z)LF	2 x 05	10.16	12.62
95290-Y06(Z)LF	2 x 06	12.70	15.16
95290-Y22(B)LF	2 x 22	53.34	55.80

- 6 - OTHERS POSITIONS, ON SPECIAL REQUEST.
7 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.

c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004

mat'l. code SEE NOTES				surface ISO 1302 ☒ ISO 406 ISO 1101		tolerance ISO 406 ISO 1101		projection 		product family DX VCC DR			
ltr	ecr	no	dr	date	tolerances unless otherwise specified						title		
E	F04-037	DLE	04.11.16		angles linear				mm		BtB RECEPT.		
F	F06-0204	DLE	06.06.28		0°±x'				scale 1/5		VERT DR SMT 8.5 mm		
G	B-19123	LMU	14.10.21		0°±x'						dwg no		
H	B-19535	BVE	14.11.24	dr	D.LEGRAND		97.01.13			sheet 2 of 2			
J	B-19923	BVE	15.01.08	enr	P.NIZZI		97.01.13			size			
				chr	P.NIZZI		97.01.13			95290			
				appd	P. NZ		97.01.13			A3			
sheet		revision											
index		sheet											