




NOTES:

1. MATERIAL:
BODY - BRONZE (GUN METAL)
SCREW - STEEL, ZINC PLATED
2. PARTS ARE cULus LISTED TO UL467 AS
GROUNDING & BONDING EQUIPMENT.
3. SEE WWW.PANDUIT.COM FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.



PART NUMBER	CONDUIT HUB SIZE	DIMENSIONS IN [mm] ±.05 [1.3]			DESCRIPTION	WATER PIPE	GROUNDING WIRE
		B	C	D			
GPC 4 - 1 - 12	1/2 "	1.65 [41.9]	1.00 [25.4]	0.56 [14.2]	GROUND CLAMP FOR RIGID CONDUIT WITH 1/2 HUB	1/2 " - 1"	8 - 4 STR
GPC 4 - 1 - 34	3/4 "	1.65 [41.9]	1.00 [25.4]	0.56 [14.2]	GROUND CLAMP FOR RIGID CONDUIT WITH STEEL SCREWS 3/4 HUB	1/2 " - 1"	8 - 4 STR
GPC 4 - 1 - 1	1"	1.65 [41.9]	1.00 [25.4]	0.56 [14.2]	GROUND CLAMP FOR RIGID CONDUIT WITH STEEL SCREWS 1 HUB	1/2 " - 1"	8 - 4 STR
GPC 4 - 2 - 12	1/2 "	2.22 [56.4]	2.08 [52.8]	1.33 [33.8]	GROUND CLAMP FOR RIGID CONDUIT WITH 1/2 HUB	1-1/4 " - 2"	8 - 4 STR
GPC 4 - 2 - 34	3/4 "	2.22 [56.4]	2.08 [52.8]	1.33 [33.8]	GROUND CLAMP FOR RIGID CONDUIT WITH STEEL SCREWS 3/4 HUB	1-1/4 " - 2"	8 - 4 STR
GPC 4 - 2 - 1	1"	2.22 [56.4]	2.08 [52.8]	1.33 [33.8]	GROUND CLAMP FOR RIGID CONDUIT WITH STEEL SCREWS 1 HUB	1-1/4 " - 2"	8 - 4 STR
GPC 4 - 4 - 12	1/2 "	4.25 [108.0]	3.81 [96.8]	2.75 [69.9]	GROUND CLAMP FOR RIGID CONDUIT WITH 1/2 HUB	2 - 1/2 " - 4"	8 - 4 STR
GPC 4 - 4 - 34	3/4 "	4.25 [108.0]	3.81 [96.8]	2.75 [69.9]	GROUND CLAMP FOR RIGID CONDUIT WITH 3/4 HUB	2 - 1/2 " - 4"	8 - 4 STR
GPC 4 - 4 - 1	1"	4.25 [108.0]	3.81 [96.8]	2.75 [69.9]	GROUND CLAMP FOR RIGID CONDUIT WITH 1 HUB	2 - 1/2 " - 4"	8 - 4 STR
GPC 4 - 6 - 12	1/2 "	5.20 [132.1]	6.00 [152.4]	2.90 [73.7]	GROUND CLAMP FOR RIGID CONDUIT WITH 1/2 HUB	4 - 1/2 " - 6"	8 - 4 STR
GPC 4 - 6 - 34	3/4 "	5.20 [132.1]	6.00 [152.4]	2.90 [73.7]	GROUND CLAMP FOR RIGID CONDUIT WITH 1/2 HUB	4 - 1/2 " - 6"	8 - 4 STR
GPC 4 - 6 - 1	1"	5.20 [132.1]	6.00 [152.4]	2.90 [73.7]	GROUND CLAMP FOR RIGID CONDUIT WITH STEEL SCREWS 1 HUB	4 - 1/2 " - 6"	8 - 4 STR

							TITLE BRONZE GROUND PIPE CLAMP CUSTOMER DRAWING					
							ITEM REVISION NAME 10J018AK/01			PANDUIT™		
							DATASET FILE NAME 10J018AK-JC/01.SLDDRW					
01	8/12	JHNU	SRBI	RGB	REVISED P/N'S: GPC4-1-12 WAS GPC6-1-12, GPC4-1-34 WAS GPC6-1-34, GPC4-1-1 WAS GPC6-1-1, GPC4-2-12 WAS GPC6-2-12, GPC4-2-34 WAS GPC6-2-34, GPC4-2-1 WAS GPC6-2-1, GPC4-4-12 WAS GPC6-4-12, GPC4-4-34 WAS GPC6-4-34, GPC4-4-1 WAS GPC 6-4-1, GPC4-6-12 WAS GPC6-6-12, GPC4-6-34 WAS GPC6-6-34, GPC4-6-1 WAS GPC6-6-1	10J018AK-JC	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XX ± .XXX ± ANGLES ±  THIRD ANGLE PROJECTION			MATERIAL SEE NOTES		
00	7/12	JHNU	SRBI	RGB	DRAWING RELEASED	10J018AK-JC				DRAWING NUMBER 10J018AK-JC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JHNU	DATE 7/12	CHK SRBI	SCALE N/A	SHEET 1 OF 1	SIZE B