

10 x 38mm Ceramic, Fast Acting




Features

- Photovoltaic / Solar Panel Power Fuses
- RoHS Compliant
- Available in Blister (B Suffix) Package



F-10



Specifications

Rated Voltage: 1000V, 690V (74-10FC20A **ONLY**)

Breaking Capacity: 1000VAC, 50A; 1000VDC, 30A

690VAC, 50A; 690VDC, 30A (74-10FC20A **ONLY**)

Time Current Characteristics:

% of Ampere Rating	Opening Time	
	1A – 5A	6A – 20A
100%	4 hours min.	4 hours min.
400%	0.003 – 1 seconds	0.01 – 10 seconds
1000%	0.02 seconds max.	0.03 seconds max.

Ordering Information:

NTE Type No. (Note 1)	Rated Current	Diag No.
74-10FC1A	1A	F-10
74-10FC2A	2A	F-10
74-10FC3A	3A	F-10
74-10FC4A	4A	F-10
74-10FC5A	5A	F-10
74-10FC6A	6A	F-10
74-10FC8A	8A	F-10
74-10FC10A	10A	F-10
74-10FC12A	12A	F-10
74-10FC15A	15A	F-10
74-10FC20A	20A	F-10

Note 1. For blister package, add a "B" suffix.