

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19200-0002](#)
Status: **Active**
Overview: [Splices](#)
Description: Avikrimp™ Seamless Butt Splice for 18-22 AWG Wire, Super Duty

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E32244

General
Product Family Splices
Series [19200](#)
Comments Red
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Splices](#)
Product Name Avikrimp™
UPC 756054241226

Physical
Barrel Type Closed
Color - Resin Red
Flammability 94V-2
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 1.593/g
Packaging Type Bag
Temperature Range - Operating 105°C
Wire Insulation Diameter 3.50mm
Wire Size AWG 18, 20, 22

Electrical
Voltage - Maximum 600V

Material Info
Old Part Number AS-845

Reference - Drawing Numbers
Product Specification PS-19902-011, PS-19902-013
Sales Drawing SD-19200-001



Series
image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19200Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
PremiumGrade™ Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19200-0002](#)