



3D VIEW



5. MATERIAL:
RECEPTACLE: PA66 GF15, GRAY
CAP: PA66 GF15, BLACK
WEDGE LOCK (INCLUDED): PBT GF30, GREEN
BUSBAR: COPPER ALLOY, NICKEL PLATED



4. THE 3 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 13 AMPS.
THE 5 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 26 AMPS.

3. ORIENTATION OF "DEUTSCH" AND "-P028" TO BE OPTIONAL.

2. BORDER SIGNIFIES THAT PINS 3,4,5,6,7 ARE BUSSED TOGETHER WITH
A 5 PIN BUSBAR AND PINS 1,2,8 ARE BUSSED TOGETHER WITH A 3
PIN BUSBAR.


1. MATES WITH DT06-08SA-XXXX (XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR MODIFICATIONS.

NOTES:



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O.PI6830	09JAN2000	-	RDR
	B	REVISER PER PCN-24-226269	06JAN2025	AJT	MB
	C	REVISED PER PCN-25-253066	15JUL2025	UBF	MB

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P.BURKE	25AUG2000	 TE Connectivity	
		CHK S.PALLUTH	1SEP2000		
		APVD S.BEARD	31AUG2000		
		PRODUCT SPEC 108-151009			
DIMENSIONS: INCHES[mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME DT 8 WAY RECEPTACLE KEY ARRANGEMENT A 5 AND 3 PIN BUSBAR - NICKEL PLATED COLOR: GREY	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025[0,63] 4 PLC ± ANGLES ±		SIZE A3	
		FINISH -		CAGE CODE 00779	
MATERIAL 5		WEIGHT 22 g		DRAWING NO C-DT04-08PA-P028	
		CUSTOMER DRAWING		RESTRICTED TO -	
		SCALE 2.000		SHEET 1 OF 1	
				REV C	