

3M™ 746 Wrist Strap Tester Properties

Property	Typical Values
Weight	7 oz. (200 g) without battery
Power	9-volt regulated 75 mA AC/DC adapter (supplied with 746)
Battery	9-volt lithium manganese (NEDA 1604LC) (supplied with 746) *does not contain mercury, cadmium, or lead.
Test Voltage	19 Volts DC, ± 1 volt (open circuit)
Resistance	Upper limit -10 M ohms $\pm 10\%$
Ranges	Lower limit -750K ohms +20% -0%
Wall Mounting	3M Dual Lock System
AC Adapter Specifications:	
Input Voltage	AC 120V
Output Voltage	DC 9 V (Regulated)
Output Current	75 mA
Output Connector Dimensions	5.5 mm (O.D.) x 2.1 mm (I.D.) x 11 mm (L)
Output Connector Polarity	Center Negative