

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

— , — .

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION.


ALL INTERNATIONAL RIGHTS RESERVED.

P.C.B. HOLE DIM. ACTION PIN

DRILLED HOLE	:	1,15	±	0,025	mm
FIN. HOLE	:	0,94	to	1,09	mm
AFTER REFLOW	:	0,91	to	1,09	mm
Cu-thks	:	0,025	to	0,075	mm
SnPb-thks	:	0,004	to	0,010	mm

NOTES:



- 1 MATERIAL CONTACT: PHOSPHORBRONZE.
MATERIAL HOUSING: GLASSFILLED THERM. POLYESTER.
- 2 AT CONTACTAREA Au OVER Ni, PERFORMANCE LEVEL I
ACC. IEC 603-2; REMAINDER Sn
- 3 AT CONTACTAREA AU OVER NI PERFORMANCE LEVEL II
ACC. IEC 603-2; REMAINDER Sn
- 4 CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE ON OUTSIDE
OF MATING AREA OF ROW d.
- 5 STAND-OFF RIBS OPTIONAL.




P Q S	ROW			
	a	b	c	d
32	X	X	X	X
31	X	X	X	X
30	X	X	X	X
29	X	X	X	X
28	X	X	X	X
27	X	X	X	X
26	X	X	X	X
25	X	X	X	X
24	X	X	X	X
23	X	X	X	X
22	X	X	X	X
21	X	X	X	X
20	X	X	X	X
19	X	X	X	X
18	X	X	X	X
17	X	X	X	X
16	X	X	X	X
15	X	X	X	X
14	X	X	X	X
13	X	X	X	X
12	X	X	X	X
11	X	X	X	X
10	X	X	X	X
9	X	X	X	X
8	X	X	X	X
7	X	X	X	X
6	X	X	X	X
5	X	X	X	X
4	X	X	X	X
3	X	X	X	X
2	X	X	X	X
1	X	X	X	X

AN ASTERISK „X” DENOTES A SIGNAL CONTACT.

LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	—	05-04-02	CB	CB
			C1	ECR-10-004467	10-03-10	GSK	MKO



			216415-4
OBSOLETE			216415-1
	FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Colpaert B.		05ARR02		 Tyco Electronics Corporation EC N.V. Oostkamp – Belgium			
		CHK Colpaert B.		05ARR02					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Colpaert B.		05ARR02		NAME 4X32 POS FEMALE B.T.B CONN. ASS'Y FOR 1,6mm P.C.BOARD THK'S	
		0 PLC ± -		PRODUCT SPEC					
		1 PLC ± -		—					
		2 PLC ± -		APPLICATION SPEC					
		3 PLC ± -		—					
		4 PLC ± -				SIZE		CAGE CODE	
		ANGLES ± -				DRAWING NO		RESTRICTED TO	
MATERIAL —		FINISH —		WEIGHT —		A300779		C-216415	
CUSTOMER DRAWING						SCALE NTS		SHEET 1 OF 1	
								REV C1	