


**BUG 10**

930 175-... (see colour index below)*

200 each




Socket with oval insulated head.
4 mm dia. nickel-plated brass
socket with dip-tinned **solder**
connection.

BO 10

930 160-... (see colour index below)*

100 each




Bright metal 4 mm dia. nickel-
plated brass socket

BU 10

930 147-... (see colour index below)*

200 each




Bright metal 4 mm dia. nickel-
plated brass socket with dip-
tinned **solder connection.**

BU 20

930 177-... (see colour index below)*

200 each



Bright metal 4 mm dia. nickel-
plated brass socket with dip-
tinned **solder connection.**

solder

ø 4 mm

solder

solder

16 A

16 A

16 A

16 A

5 mΩ

5 mΩ

5 mΩ

5 mΩ

-25 °C... +85 °C

-25 °C... +100 °C

-25 °C... +100 °C

-25 °C... +100 °C

-100

-101

-102

-103

-104

-000

-000

-000