



4250IND

NON-CONDUCTIVE

- Heavy duty rubber housing minimizes risk of electrical shock



NON-SLIP

- Square construction prevents rolling
- Textured handle area for secure grip



DURABLE

- Survives 7' drop test



FACETED REFLECTOR

- Provides wide, high-quality spot



A heavy duty rubber case makes the 4250IND ideal as a non-conductive lighting tool for electrical applications. In addition, it is safe to use for plumbing and wet areas.

A built-in lanyard and clip easily hangs the light from nearby pipes or other protrusions. With an improved, faceted reflector, you can count on this light for a wide, high-quality spot.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation:	Contractor 2 D Ultra Grip Rubber Light
Model:	4250IND
Color:	Black and Yellow
Power Source:	Two "D"
ANSI / NEDA:	13 Series
Lamp:	KPR-102 Krypton beam
Lamp Rating:	2.4V, 0.7A
Lamp Life:	15 Hours
Lamp Output:	16.5 Lumens
Durability:	Survives 7 foot drop
Typical Weight:	324 grams (11.4 oz.) (without batteries)
Dimensions (in):	8.19 x 3.15

Performance:



Important Notice

This datasheet contains information specific to products manufactured at the time of its publication

Contents herein do not constitute a warranty
©Energizer / All Rights Reserved