


MALLORY**Mallory Sonalert Products Inc.****Part # SC628AFJ****Sales Outline Drawing****Revision B****Specifications:**

Sound level Category	Low Sound Level
Mode of Operation	Slow Pulse
Mounting	Panel (see note B)
Voltage Rating	6 to 28 Vac/dc
Frequency	2900 Hz \pm 500 Hz
Loudness (Min. Voltage)	55/68 dB(A) min @ 2 FT and 6 Vac/dc
Loudness (Max Voltage)	70/80 dB(A) min @ 2FT and 28 Vac/dc
Current Draw	2 mA Max @ 6 Vac/dc
Current Draw	8 mA Max @ 28 Vac/dc
Min. Pulse Rate (PPS)	0.5 @ 6 Vac/dc
Max. Pulse Rate (PPS)	2 @ 28 Vac/dc
Duty Cycle (%)	50 (Approx)
Storage Temperature	-40°C to +85°C
Operating Temperature	-30°C to +65°C
Weight (Typical)	2.7 oz (76 g)
Housing	6/6 Nylon, Color Black
Options	For other options contact factory

Dimensions: Inches (mm)

NOTE A: TERMINALS-.032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4" QUICK CONNECT.

NOTE B: MOUNTING- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 1.25" HOLE PUNCHED IN PANEL, IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SC628AFJ](#)