

184-33004



Article Number: 184-33004

High Density Slotted Wall Wiring Duct, 3" X 3", Non-Adhesive, PVC, White, 120ft/Carton

RoHS

Download drawing

Download spec sheet

Base Data

Local Order Number	184-33004
Type	SLHD3X3
Color	White (WH)
Features and Benefits	• Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance. • Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation. • Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.
Product Description	Pro-Duct high density, slotted wiring duct features narrow fingers, a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.
Short Description	High Density Slotted Wall Wiring Duct, 3" X 3", Non-Adhesive, PVC, White, 120ft/Carton

Product Dimensions

Length L (Imperial)	6.0 ft
Length L (Metric)	1.83 m
Width W (Imperial)	3.0 "
Width W (Metric)	76.2 mm
Width W2 (Imperial)	3.0 "
Width W2 (Metric)	76.2 mm
Width W3 (Imperial)	0.16 "
Width W3 (Metric)	4.1 mm
Width W4 (imperial)	0.4 "
Width W4 (metric)	10.2 mm
Width W5 (imperial)	2.6 "
Width W5 (metric)	66.0 mm
Width W6 (imperial)	1.0 "
Width W6 (metric)	25.4 mm
Height H (Imperial)	3.07 "
Height H (Metric)	77.9 mm
Mounting Hole Centers (Imperial)	2.0 "

Logistics and Packaging

Quantity Per	carton
Package Quantity	120.0 ft

Package Quantity (Metric) 36.6 m

Carton Quantity 120.0 ft

Material and Specifications

Material Polyvinylchloride (PVC)

Material Shortcut PVC

Flammability self-extinguishing

Operating Temperature +122°F (+50°C)

ROHS Compliant Yes

Certification/Specification UL
CSA

UL Listed (US and Canada) No

UL Recognized (US) Yes

UL Recognized (US and Canada) No