





SPECIFICATION

MATERIALS:

HOUSING & INSERT: PBT

COUPLING: BRASS-NICKEL PLATED

O-RING: VITON

ELECTRICAL:

VOLTAGE: 10-30VDC

CURRENT RATING: 4A PER PORT, 12 AMPS MAX.

PROTECTION CLASS: IP68

NOTES:

THREADED PLUG FITTED TO PORTS 1 & 2 ONLY

PROTECTION CAP FITTED TO ALL M12 PORTS

FIXING HOLES TO SUIT M4 SCREWS

SAP-Nummer	alte Artikel-Nr.	Beschreibung	Farbe
SAP-NUMBER	OLD ENGINEERING-No.	DESCRIPTION	COLOR
1201190027	BKY400P-FBP-03	ULTRA-LOCK MPIS 4 WAY - 4 I/O 3M	gelb/YELLOW
1201190001	BKY400P-FBP-05	ULTRA-LOCK MPIS 4 WAY - 4 I/O 5M	gelb/YELLOW
1200550891	BKY400P-FBP-10	ULTRA-LOCK MPIS 4 WAY - 4 I/O 10M	gelb/YELLOW

NEW RELEASE EC NO: WEU2010-0220 DRWN:SBH CHKD: APPR:FPACHER	2009/12/07 2009/12/17 2009/12/18	DESCRIPTION REV
---	--	--------------------

QUALITY SYMBOLS	
	=0
	=0
GENERAL TOLERANCES (UNLESS SPECIFIED)	
	mm
4 PLACES	± ---
3 PLACES	± ---
2 PLACES	± 0.05
1 PLACE	± 0.10
ANGULAR ± ---°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
SBH	2009/12/10
CHECKED BY	DATE
APOHL_WEU	2009/12/10
APPROVED BY	DATE
FPACHER	2009/12/17
MATERIAL NO.	
SEE TABLE	
SIZE	A3

SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
TITLE ULTRA-LOCK MPIS 4 WAY - 4 I/O XM-PUR		
MOLEX INCORPORATED		
DOCUMENT NO. SD-120119-017		
SHEET NO. 1 OF 1		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		