


TECHNICAL SPECIFICATIONS

Materials:**Unshielded Hood:** UL-recognised plastic material**Operating Temperature:** -30°C to +110°C**Colour:** Black (Standard)
Other colour on request**Shielded Hood:** UL-recognised plastic material**Plating:** Nickel over Copper**Operating Temperature:** -30°C to +90°C**Thumbscrews:** UNC 4-40 (Standard)**Features:**

- Available in sizes 9 and 25 (15 on request)
- Available in EMI-shielded and unshielded version
- Delivered complete with wires and Sub-D
- Pre-wired connectors on request



Size MHDA	Dim A	Dim B	Dim C
9-way	33,0	15,0	49,5
15-way	41,3	15,0	39,0
25-way	55,1	15,0	39,0

Ordering information:

Unshielded Version

Size:	P/N - Kitted:	Product Code:
9-way	2112-0100-01	DA09-SMJ6-K-RC
25-way	2112-0100-03	DA25-SMJ6-K-RC
9-way	2112-0100-11	DA09-PMJ6-K-RC
25-way	2112-0100-13	DA25-PMJ6-K-RC
9-way	2112-0101-01	DA09-SMJ8-K-RC
25-way	2112-0101-03	DA25-SMJ8-K-RC
9-way	2112-0101-11	DA09-PMJ8-K-RC
25-way	2112-0101-13	DA25-PMJ8-K-RC