


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.  
NOTES:

1. APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 200 LBS [ 889 NEWTONS ]  
WHEN TESTED ON A 1.5" MANDREL
3. BRACKETS [ ] DENOTES DIMENSIONS IN MILLIMETERS  
AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:  
.XXX =  $\pm .010$  [ .25 ] .XX =  $\pm .02$  [ .5 ]  
.X =  $\pm .03$  [ .8 ] ANGLES =  $\pm 2^\circ$
5. MATERIAL: 304 STAINLESS STEEL

| PANDUIT<br>PART NO. | MAX BUNDLE<br>DIAMETER | PACKAGE<br>QTY | LENGTH<br>L = $\pm .3$ [ 7 ] |
|---------------------|------------------------|----------------|------------------------------|
| MLT1S-CP            | 1" [ 25 ]              | 100            | 5.0" [ 127 ]                 |
| MLT2S-CP            | 2" [ 51 ]              | 100            | 7.9" [ 201 ]                 |
| MLT2.7S-CP          | 2.7" [ 69 ]            | 100            | 10.2" [ 259 ]                |
| MLT4S-CP            | 4" [ 102 ]             | 100            | 14.3" [ 362 ]                |
| MLT6S-CP            | 6" [ 152 ]             | 100            | 20.5" [ 521 ]                |
| MLT8S-CP            | 8" [ 203 ]             | 100            | 26.8" [ 679 ]                |
| MLT10S-CP           | 10" [ 254 ]            | 100            | 33.0" [ 838 ]                |
| MLT12S-Q            | 12" [ 304 ]            | 25             | 39.3" [ 998 ]                |
| MLT14S-Q            | 14" [ 355 ]            | 25             | 45.5" [ 1156 ]               |
| MLT15S-Q            | 15" [ 380 ]            | 25             | 49.2" [ 1250 ]               |
| MLT2S-L             | 2" [ 51 ]              | 50             | 7.9" [ 201 ]                 |
| MLT4S-L             | 4" [ 102 ]             | 50             | 14.3" [ 362 ]                |



|     |      |      |      |      |                                                                       |            |                                                                                                                                                 |  |                    |                                      |              |            |           |
|-----|------|------|------|------|-----------------------------------------------------------------------|------------|-------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------|--------------------------------------|--------------|------------|-----------|
|     |      |      |      |      |                                                                       |            | TITLE<br>METAL LOCKING TIE STANDARD<br>SERIES 304 STAINLESS STEEL<br>CUSTOMER DRAWING                                                           |  |                    |                                      |              |            |           |
|     |      |      |      |      |                                                                       |            | ITEM REVISION NAME<br>N41119BS/11                                                                                                               |  | <div>PANDUIT</div> |                                      |              |            |           |
|     |      |      |      |      |                                                                       |            | DATASET FILE NAME<br>N41119BS_DC/11A                                                                                                            |  |                    |                                      |              |            |           |
|     |      |      |      |      |                                                                       |            | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ]<br>.x ± .1 [ 2.54 ] .xxx ± .005 [ .127 ]<br>.xx ± .01 [ .25 ] ANGLES ± 5 ° |  |                    | MATERIAL:<br><br>304 STAINLESS STEEL |              |            |           |
|     |      |      |      |      |                                                                       |            | <div><div><div></div></div><div><div></div></div></div> THIRD ANGLE<br>PROJECTION                                                               |  |                    | DRAWING NUMBER:<br>N41119BS_DC       |              |            |           |
|     |      |      |      |      |                                                                       |            | DRAWN BY<br>JAMB                                                                                                                                |  | DATE<br>2/12       | CHK<br>DPN                           | SCALE<br>2:1 | SHT 1 OF 1 | SIZE<br>A |
| REV | DATE | BY   | CHK  | APR  | DESCRIPTION                                                           | ECN        |                                                                                                                                                 |  |                    |                                      |              |            |           |
| 11A | 3/13 | JAMB | MIM  | RGRO | UPDATE DRAWING TO NEW GLOBAL PANDUIT<br>TITLE BLOCK WITH PANDUIT LOGO | SSECN01037 |                                                                                                                                                 |  |                    |                                      |              |            |           |
| 10A | 2/12 | MIM  | RGRO | ---  | NOTE #3 METRIC DIMENSIONS NOTED AS BEING<br>SHOWN FOR REFERENCE ONLY  | -----      |                                                                                                                                                 |  |                    |                                      |              |            |           |