


# samtec

HLS-0308-G-2



## CARRIER STRIPS HLS & HLT SERIES

### Mates with:

TS-1, HTS, BBS, BBL, BHS, BBD, BDL, LBS, HLT, TSB

Lead sockets "float" and "self-center" when this low profile carrier is soldered. Ideal for most VP or IR processes.

### SPECIFICATIONS


For complete specifications see [www.samtec.com?HLS](http://www.samtec.com?HLS)

Same as SL-1 except:  
**Insulator Material:** Black High Temperature Thermoplastic  
**Temperature Range:** -55°C to +140°C  
**Heat Deflection Temp:** 215°C @ 264 psi

### Note:

This Series is non-standard, non-returnable.


| HLS                                      | NO. ROWS | NO. PINS PER ROW                    | PLATING OPTION                                                                     | LEAD STYLE | OPTION                 |
|------------------------------------------|----------|-------------------------------------|------------------------------------------------------------------------------------|------------|------------------------|
| Total Pins = No. Rows x No. Pins Per Row |          | -01 thru -20 (requires both digits) | -G<br>= 30μ" (0,76μm) Gold Contact<br>10μ" (0,25μm) Gold Shell                     |            | -L<br>= Locking Socket |
|                                          |          |                                     | -T<br>= 30μ" (0,76μm) Gold Contact<br>Tin Shell                                    |            |                        |
|                                          |          |                                     | -S<br>= 10μ" (0,25μm) Gold Contact<br>Tin Shell (Styles 2 & 22 only)               |            |                        |
|                                          |          |                                     | -TT<br>= Tin Contact and Shell<br>(Styles 2, 10, 11, 12, 18, 22, 30, 31 & 32 only) |            |                        |



Total Pins = No. Rows x No. Pins Per Row

Low Insertion Force (LIF) Available


### -2 or -18 = Standard Socket For LIF specify -22 or -38




\*Locking Lead Available. See Option.

Lead DIA Accepted = .015" to .022"  
 Insertion Depth = .095" to .150"  
 Style 2 Component Part No. = SC-1P1  
 Style 22 Component Part No. = EZ-1P1  
 Style 18 Component Part No. = SC-6P1  
 Style 38 Component Part No. = EZ-6P1


### -3 = Body Only For LIF specify -23




### -10 = Low Profile Hollow Leg For LIF specify -30




### -11 = Low Profile Standard For LIF specify -31



### -12 = Micro Socket For LIF specify -32



### -14 or -15 = Short Tail



Mates with:  
 SS-1, SD-1, HSS, SL, SDL, ESS, ESD, HLS

### SPECIFICATIONS





For complete specifications see [www.samtec.com?HLT](http://www.samtec.com?HLT)

Same as HLS except:  
**Terminal Material:** Brass  
**Plating:** Au or Sn over 50μ" (1,27μm) Ni  
**Current Rating:** 1A

### Note:

This Series is non-standard, non-returnable.

| HLT                                      | NO. ROWS | NO. PINS PER ROW                    | PLATING OPTION               | LEAD STYLE      |
|------------------------------------------|----------|-------------------------------------|------------------------------|-----------------|
| Total Pins = No. Rows x No. Pins Per Row |          | -01 thru -20 (requires both digits) | -G<br>= 20 μ" (0,51 μm) Gold | -R              |
|                                          |          | 01 thru 20 (requires both digits)   | -T<br>= Tin                  | -H              |
|                                          |          |                                     |                              | -T = Short Tail |



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047  
 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299  
 SAMTEC SCANDINAVIA • Tel: +46-84477280 • Fax: +46-847420413  
 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502  
 SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842  
 SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340  
 SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681  
 SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520  
 SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61  
 SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-61103766  
 SAMTEC SOUTH AFRICA • Tel: 27 11 4528112 • Fax: 27 86 6714432  
 SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113  
 SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315  
 SAMTEC INDIA • Tel: 91 80 306 21 612 • Fax: 91 80 4152 8187  
 SAMTEC TAIWAN • Tel: 886 02 2698-3367 • Fax: 886 02 8698-2159  
 SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745