






LOC		DIST		REVISIONS				
DF	FO	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			J	TYCO LOGO REPLACED WITH THE AMP BRAND LOGO	28APR11	CT	DH	



- 1 AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.
- 2 STANDOFFS: POSN 10 (8) STANDOFFS AS SHOWN.
POSN 14 (11) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 18 (14) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 22 (17) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 26 (20) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 30 (23) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 34 (26) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 38 (29) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 42 (32) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 46 (35) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 50 (38) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 54 (41) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 58 (44) STANDOFFS, 3 PER DIAGONAL ROW.

- 3 FINISH: BRIGHT TIN-LEAD .000100-.000200 THK OVER NICKEL .000050 MIN THK.
- 4 HEIGHT AFTER TERMINATION IS .238 REF.
- 5 FINISH: BRIGHT TIN .000100-.000200 THK OVER NICKEL .000050 MIN THK.



	5	2.450	2.450	2.774	2.450	2.450	49	50	6-111037-1
	5	1.650	1.650	1.974	1.650	1.650	33	34	5-111037-7
	5	1.450	1.450	1.774	1.450	1.450	29	30	5-111037-6
	5	1.250	1.250	1.574	1.250	1.250	25	26	5-111037-5
	5	.650	.650	.974	.650	.650	13	14	5-111037-2
	5	.450	.450	.774	.450	.450	9	10	5-111037-1
OBSOLETE	3	2.850	2.850	3.174	2.850	2.850	57	58	1-111037-3
OBSOLETE	3	2.650	2.650	2.974	2.650	2.650	53	54	1-111037-2
	3	2.450	2.450	2.774	2.450	2.450	49	50	1-111037-1
OBSOLETE	3	2.250	2.250	2.574	2.250	2.250	45	46	1-111037-0
OBSOLETE	3	2.050	2.050	2.374	2.050	2.050	41	42	111037-9
OBSOLETE	3	1.850	1.850	2.174	1.850	1.850	37	38	111037-8
	3	1.650	1.650	1.974	1.650	1.650	33	34	111037-7
	3	1.450	1.450	1.774	1.450	1.450	29	30	111037-6
	3	1.250	1.250	1.574	1.250	1.250	25	26	111037-5
OBSOLETE	3	1.050	1.050	1.374	1.050	1.050	21	22	111037-4
OBSOLETE	3	.850	.850	1.174	.850	.850	17	18	111037-3
	3	.650	.650	.974	.650	.650	13	14	111037-2
	3	.450	.450	.774	.450	.450	9	10	111037-1
FINISH	F	E	D	C	B	A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J. PEACHEY 05-MAR-86
CHK M. SCULLY 23-MAY-86

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± .005
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL
HOLDED PARTS: 94V-0 RATED
THERMOPLASTIC COLOR BLACK
CONTACTS: PH BRZ PER QQ-B-750

FINISH
CONTACTS
3

APPROD D. HOFFMAN 23-MAY-86
NAME
PRODUCT SPEC
APPLICATION SPEC
114-40005

SIZE CAGE CODE DRAWING NO
A1 00779 111037

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE 10:1 SHEET 1 OF 1 REV J