




INTERFAN[®]

Tubeaxial Cooling Fans, Radial Blowers & Heat Sink Fans

Featuring:

Ball Bearing Dependability

International Safety Standards

Locked Rotor and Polarity Protection

Custom Cable/Connector Assemblies

Silent Operation

- Long-life, ball bearing construction
- Locked rotor and polarity protection
- Silent operation
- Industry standard frames and mounting
- Meets or exceeds safety standards
- Custom cable/connector assemblies
- Sensor fans available (special order)



AC Fans

Frame Size H x W x D mm (inches)	Model	Voltage (V)	Airflow (CFM)	Input Power (Watts)	Speed (RPM)	Noise Level (dBA)	Weight (Oz)	Construction	Guard Filter Cord
80 x 80 x 25 (3.2 x 3.2 x 1.0)	PM033-115-8025B-4 PM033-230-8025B-4	115 230	33	10.0	2700	33	6.8	Aluminum housing, plastic impeller, sealed ball bearing 22AWG wire leads	5508 80FP-45 5505
80 x 80 x 38 (3.2 x 3.2 x 1.5)	PM037-115-8038BT-4 PM037-230-8038BT-4	115 230	37	12.0	2700	39	10.3	Aluminum alloy housing, plastic impeller, sealed ball bearing, terminal block	5508 80FP-45 5505
92 x 92 x 25 (3.6 x 3.6 x 1.0)	PM040-115-9225BT-4 PM040-230-9225BT-4	115 230	40	12.0	2400	39	8.0	Aluminum housing, plastic impeller, sealed ball bearing, terminal block	5520 92FP-45 5505
120 x 120 x 25 (4.7 x 4.7 x 1.0)	PM053-115-1225BT-4 PM053-230-1225BT-4	115 230	53	13.0	1900	38	11.8	Aluminum housing, plastic impeller, sealed ball bearing, terminal block	5504 5502
	PM080-115-1225BT-4 PM080-230-1225BT-4	115 230	80	18.0	2300 2900	45	11.8		120FP-45 5505
120 x 120 x 38 (4.7 x 4.7 x 1.5)	PM115-115-1238BT-4 PM115-230-1238BT-4	115 230	115	20.0	3000	49	18.2	Aluminum housing, plastic impeller, sealed ball bearing, terminal block	5504 5502 120FP-45 5505
172 x 150 x 38 (6.8 x 6.0 x 1.0)	PM220-115-1738BT-4 PM220-230-1738BT-4	115 230	220	32.0 38.0	3100	52	31.0	Aluminum housing, plastic impeller, sealed ball bearing, terminal block	5506 5505
172 x 150 x 51 (6.8 x 6.0 x 2.0)	PM238-115-1751BT-4 PM238-230-1751BT-4	115 230	238	32.0 38.0	3100	55	33.3	Aluminum housing, plastic impeller, sealed ball bearing, terminal block	5506 5505

AC Radial Blowers

120 x 120 x 38 (4.8 x 4.8 x 1.5)	PMB24-115-4B PMB24-230-4B	115 230	24	20.0	2300	53	23.0	Plastic housing, plastic wheel, sealed ball bearing, 20 AWG wire leads	N/A
--	------------------------------	------------	----	------	------	----	------	--	-----

Accessories

Product Type	Part Number	Fan Compatibility	Construction
Finger Guards	5514	40 mm	Nickel chrome plated wire guards, spot welded
	5516	60 mm	
	5508	80 mm	
	5520	92 mm	
	5504	120 mm	
	5506	162 mm	
Filter Guards	60FGM	60 mm	Metal mesh filter
	80FGM	80 mm	
	92FGM	92 mm	
	120FGM	120 mm	
	162FGM	162 mm	
Plastic Filter Guards	40FP-45	40 mm	Plastic filter and finger guard assembly (45PPI foam filter media)
	60FP-45	60 mm	
	80-FP-45	80 mm	
	92FP-45	92 mm	
	120FP-45	120 mm	
	162FP-45	162 mm	
Cords	5505	—	24" (straight) plug and cord for terminal block; blunt cut ends
	5505-45D	—	24" (45°) plug and cord for terminal block; blunt cut ends