


(2,00 mm) .0787"

(2,54 mm) .100"

BTMM, BTSW SERIES



LOW PROFILE SQUARE POST JUMPER

SPECIFICATIONS

For complete specifications
see www.samtec.com?BTMM

Insulator Material:

Black Liquid

Crystal Polymer

Terminal Material

Phosphor Bronze

Plating:

Sn over 50μ" (1.27 μm) Ni

Operating Temp


-55°C to +105°C
RoHS Compliant

Rot
Yes

Lead-Free Solderable:

Lea
Yes

163



Note: Some sizes, styles and options are non-standard, non-returnable

SPECIFICATIONS

For complete specifications
see www.samtec.com?BTSW

Insulator Material:

Black Glass Filled

Polyester Terminal

Terminal Material:
Phosphor Bronze

Phosphor Bronze Plating:

Sn over 50μ" (1,27 μm) Ni

Operating Temp
55°C to 125°C


-55°C to +105°C
RoHS Compliant.

Yes


Lead-Free Solderable:

**Lead-Free
Wave Only**

APPLICATION



Note: Some sizes, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 **SAMTEC NORTHERN CALIFORNIA** • Tel: 408-395-5900 **SAMTEC SOUTHERN CALIFORNIA** • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA. • Tel: +55 31 3786 3227 **SAMTEC UNITED KINGDOM** • Tel: +44 2126 739292 **SAMTEC GERMANY** • Tel: +49 (0) 89 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 **SAMTEC ITALY** • Tel: 39 039 6890337 **SAMTEC NORDIC/BALTIC** • Tel: +46 84477280 **SAMTEC BENELUX** • Tel: +44 2126 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 **SAMTEC INDIA** • Tel: +91-80-3272 1612 **SAMTEC ASIA PACIFIC** • Tel: 65 6745-5955 **SAMTEC JAPAN** • Tel: 045-475-1385 **SAMTEC CHINA** • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 **SAMTEC HONG KONG** • Tel: 852-26094858 **SAMTEC KOREA** • Tel: 82-31-717-5685 **SAMTEC ANZ** • Tel: 613 9580 0683