


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		D	REVISE PER ECO-05-006320	01AUG05	TW	JH

Tooling Drawing NO.
USB A: TR00662
USB B: TR00664



PIN ASSIGNMENT :

USB A	2	3	1	4	Shell
	Pair 1				
	White(D-)	Green(D+)	Red(V _{bus})	Black(Gnd)	Drain Braid
USB B	2	3	1	4	Shell



PART NO.	1487597-1	1487597-2	1487597-3
LENGTH(L)	3000	2500	3500

NOTES:

1. TESTED FOR CONTINUITY, SHORTS AND OPENS, HI-POT 630V FOR 10MS.
2. CABLE ASSEMBLY MEETS USB 2.0 STANDARDS.
3. EXPOSED CABLE BRAID IS NOT PERMISSIBLE BEYOND OVERMOLD.
4. THE FINAL CABLE ASSEMBLY MAXIMUM LENGTH NOT TO EXCEED 4300MM PER USB SPECIFICATIONS.
5. MEETS REQUIREMENTS OF EU DIRECTIVE 2002/95/EC

AR	AR	AR	MR	COPPER FOIL, W: 5MM	6
1	1	1	PC	LABEL, 25x35mm, White 25x13mm	5
AR	AR	AR	KG	Overmold PVC, 40P, Color: Black(BK01)	4
AR	AR	AR	MR	USB 2.0 Cable 25AWG*1P+22AWG*2C+Al/Mylar +Drain+Braid, Color: Black(BK01).	3
1	1	1	EA	USB 4Pin Connector Contacts: Gold 30U Plated, Shell: Nickel Plated, Housing UL94V-0 B Type.	2
1	1	1	EA	USB 4Pin Connector Contacts: Gold 30U Plated, Shell: Nickel Plated, Housing UL94V-0 A Type.	1
-3	-2	-1	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BOVEY LIU	25/FEB/02	tyco Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: mm		CHK —	—	NAME CABLE ASSEMBLY, USB A TYPE TO USB B TYPE		
		APVD F.D. McCORKEL	15/MAR/02	—		
		PRODUCT SPEC		—		
MATERIAL —		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO
		WEIGHT —		A3	00779	C-1487597
FINISH —		CUSTOMER DRAWING			SCALE N.T.S	SHEET 1 OF 1
					REV D	