


Block & Tackle

Klein's line of block and tackle is engineered for high-strength requirements.



For Professionals...
Since 1857™



- These are NOT occupational protective devices. NOT for human support.
- Sheaves are strong, yet lightweight aluminum alloy with all-bronze bushings.
- Light, galvanized-steel shell blocks are fitted with snubbing hooks to hold the load.
- All Klein block and tackle use high-quality, 3/8" diameter rope.
- Available with standard snap hooks or guarded snap hooks (with snap hook nose lengthened to extend over the latch or keeper).
- Choice of forged hook Cat. No. 258 or swivel hook Cat. No. 259.
- Catalog numbers followed by S/R have rope spliced to block.
- Maximum safe load is 750 lbs. (338 kg).

Anchor Hook

- Forged hook is designed to fit under insulator and engage pin of cross arm
- Maximum safe load 750 lbs. (340 kg)



258

Cat. No.	Eye I.D.	Throat Opening	Overall Length	Weight
258	5/8" (15.9 mm)	1-7/8" (47.6 mm)	5-1/2" (139.7 mm)	6.7 oz. (191 g)

Heavy-Duty Snap Hook

- Snaps on with one hand
- Forged hook may be used on many conventional steel blocks, 4" (102 mm) or smaller
- Maximum safe load 8000 lbs. (3629 kg)



455

Cat. No.	Eye I.D.	Throat Opening	Overall Length	Weight
455	15/16" (23.8 mm)	1" (25.4 mm)	5" (127.0 mm)	13.4 oz. (381 g)

Swivel Anchor Hook

- Swivel clevis on this forged hook will engage with snap on Klein block & tackle Cat. Nos. 1802-30 and H1802-30
- Swivel prevents twisting and kinking of rope
- Cat. No. 470 has plunger latch
- Maximum safe load 750 lbs. (340 kg)



259

Cat. No.	Swivel Opening	Throat Opening	Overall Length	Weight
259	1-3/16" x 1" (30.2 x 25.4 mm)	1-7/8" (47.6 mm)	6-1/2" (165.1 mm)	6.4 oz. (181 g)
470	1-3/16" x 1" (30.2 x 25.4 mm)	5/8" (15.9 mm)	5" (127.0 mm)	4.8 oz. (136 g)

Rope



48502

- Works with all block and tackle products
- High-quality, 3/8" diameter rope
- Maximum safe load 750 lbs. (340 kg)

Cat. No.	Diameter	Average Strength	Minimum Strength	Overall Length	Weight
48502	3/8" (9.5 mm)	3600 lbs. (1632 kg)	3200 lbs. (1500 kg)	25 ft. (7.6 m)	12.5 oz. (354 g)

Blocks

- Blocks without ropes and hooks
- Made of light galvanized steel and aluminum alloy
- Sheaves have bronze bushings
- Maximum safe load 750 lbs. (340 kg)



267



268



H267



H268

Cat. No.	Description	Weight
267	Self-locking Block Without Rope and Hook	12.2 oz. (346 g)
H267	Block with Nose Extended Over Keeper	12.8 oz. (363 g)
268	Block with Eye to Splice Line to Block	14.4 oz. (408 g)
H268	Block with Eye and Nose Extended Over Keeper	1.0 lbs. (0.45 kg)

Block & Tackle Packages

Block and Tackle with Standard Hooks



Cat. No.	267 Block	268 Block	258 Anchor Hook	259 Swivel Anchor Hook	Rope spliced to component number	Weight
1802-30	●	●	●			2.80 lbs. (1.27 kg)
1802-30SR	●	●	●		268 Block	2.75 lbs. (1.25 kg)
1802-30S	●	●		●		2.85 lbs. (1.29 kg)
1802-30SSR	●	●		●	268 Block	2.85 lbs. (1.29 kg)



1802-30




1802-30 S/R



1802-30S




1802-30S S/R



Block & Tackle Packages

Block and Tackle with Guarded Hooks



Cat. No.	H267 Block	H268 Block	258 Anchor Hook	259 Swivel Anchor Hook	Rope spliced to component number	Weight
H1802-30	●	●	●			2.90 lbs. (1.32 kg)
H1802-30SR	●	●	●		H268 Block	2.75 lbs. (1.25 kg)
H1802-30S	●	●		●		3.00 lbs. (1.36 kg)
H1802-30SSR	●	●		●	H268 Block	3.00 lbs. (1.36 kg)



H1802-30



H1802-30 S/R



H1802-30S



H1802-30S S/R

Block & Tackle

Polypropylene Hand-Lines with Snap Hook



1804-60

- Made of 5/16" (7.9 mm) three-strand polypropylene rope spliced to eye of snap hook
- Both lines 75' (23 m) long
- Forged steel with swivel clevis and quick-acting plunger-style latch
- Maximum safe load 250 lbs. (113 kg)

Cat. No.	Description	Includes	Weight
1803-60	Polypropylene Hand-Line with Snap Hook	Cat. No. 443A Snap	2.5 lbs. (1.13 kg)
1804-60	Polypropylene Hand-Line with Swivel Hook	Cat. No. 470 Swivel Snap	2.2 lbs. (1.00 kg)

Howe Wire Tool

- Strap is made of tough Klein-Kord™
- Swivel hook is forged steel with large opening
- Shank of hook is lengthened to reach under insulator
- Other end has device to hold the load at any distance
- All metal parts are galvanized
- Max. safe load 500 lbs. (225 kg)



1702-20N

Cat. No.	Length	Width	Weight
1702-20N	7 ft. (2.1 m)	1" (25.4 mm)	2.0 lbs. (0.91 kg)

Snap Hook

- General-purpose forged snap hook with eye at 90° to opening
- Maximum safe load 1500 lbs. (675 kg)



443A

Cat. No.	Eye I.D.	Throat Opening	Overall Length	Weight
443A	1" (25.4 mm)	1/2" (12.7 mm)	5-1/2" (139.7 mm)	8.3 oz. (235 g)

Swivel Snap Hook



2012

- This is NOT an occupational protective hook. NOT for human support
- Bronze swivel snap hook made for use on canvas buckets
- Maximum safe load 150 lbs. (68 kg)

Cat. No.	Length	Width	Weight
2012	4-3/8" (111.1 mm)	1-5/8" (41.3 mm)	4.5 oz. (128 g)

Web Strap Ratchet Hoist

- Large, non-conductive drum knob allows web slack to be adjusted with ease
- 360° handle rotation
- 3/4 ton single line and 1-1/2 ton double line load rating
- Tight ratcheting mechanism allows precise tensioning
- Meets ANSI/ASME B30.21-2005 & B30.10-2009 standards

Cat. No.	Weight
KN1500PEX	12.50 lbs. (5.67 kg)
KN1500PEXH	13.60 lbs. (6.17 kg)



- **Single Line Load Rating:** 1500 lbs. (675 kg)
Min. to Max. Pulling Distance inches (mm):
20" (500 mm) - 138" (3500 mm)



- **Double Line Load Rating:** 3000 lbs. (1350 kg)
Min. to Max. Pulling Distance inches (mm):
26" (700 mm) - 79" (2000 mm)



KN1500P-EX