



# Electr. Installation Multi-Tone



Surface housing (accessory)



Bracket (accessory)

- Loud installation multi-tone sounder for the 22.5 mm control panel programme
- High protection rating IP 65
- Adjustable to 8 different tones
- Adjustable sound output

## TECHNICAL SPECIFICATIONS:

**Dimensions** (Diameter x Depth): 70 mm x 71.6 mm

**Housing:** PC/ABS-Blend; Deckel: PC

**Sound output:** max. 100 dB (sound output is adjustable on rear side when mounted)

**Tone type:** 8 tones adjustable on rear side of the housing

|  |                   |  |         |            |
|--|-------------------|--|---------|------------|
|  | Switch position 0 |  | 1,6 kHz | 86 dB (A)  |
|  | Switch position 1 |  | 1,6 kHz | 86 dB (A)  |
|  | Switch position 2 |  | 1,6 kHz | 86 dB (A)  |
|  | Switch position 3 |  | 1,6 kHz | 88 dB (A)  |
|  | Switch position 4 |  | 3,4 kHz | 90 dB (A)  |
|  | Switch position 5 |  | 3,4 kHz | 100 dB (A) |
|  | Switch position 6 |  | 3,4 kHz | 96 dB (A)  |
|  | Switch position 7 |  | 3,4 kHz | 100 dB (A) |

**Fixing:**

**Connection:**

**Life duration:**

Installation mounting for  $\varnothing$  22.5 mm (M 22) with anti-twist device  
Connector plug with screwable connection max. 1.5 mm<sup>2</sup>  
> 5,000 hrs

## ORDER SPECIFICATIONS:


|                     |                |              |              |
|---------------------|----------------|--------------|--------------|
| Voltage             | 24 V $\approx$ | 115 V $\sim$ | 230 V $\sim$ |
| Current consumption | 80 mA          | 40 mA        | 40 mA        |
|                     | 110 000 75     | 110 000 67   | 110 000 68   |

## ACCESSORIES:

|                                                                                            |            |
|--------------------------------------------------------------------------------------------|------------|
| Bracket with protective cap (IP 54)                                                        | 975 109 01 |
| Surface housing IP 65 (single)                                                             | 975 109 02 |
| Surface housing IP 65 (double)<br>for 1 beacon and<br>1 audible element                    | 975 109 03 |
| Surface housing IP 65 (triple)<br>for 2 beacons and<br>1 audible element<br>(see page 108) | 975 109 04 |
| Surface housing IP 65 (quadruple)                                                          | 975 109 05 |




## TECHNICAL DIAGRAMS

see page 140







# Technical Diagrams

Electronic Installation Buzzer 109



Electronic Installation Buzzer



110

Electronic Installation Multi-tone Sounder

