




4





3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION JAN , 2007. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
J				SEE SHEET 1		




カバーテープリーダー部
外周1巻
WIDE COVER TAPE AROUND
OUT PERIPHERY 1 TURN
剥離強度 0.1-1.3N MAX(300±10mm/min)
PEELING STRENGTH
剥離角度 165~180°
PEELING ANGLE

引き出し方向
TOP OF REEL

1000個/リール
1000EA/REEL

HOLES
8穴

空 部
WITHOUT CHARGE
300mm程度
APPROX
製品装填部
WITH PRODUCT CHARGE
600mm程度
APPROX
空 部
WITHOUT CHARGE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	—	 TE Connectivity		
		CHK	—			
		APVD	—	NAME 名称		
DIMENSIONS: 単位: 耗 MM		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		MICRO USB RECEPTACLE STANDARD TYPE B ASSY		
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH 仕上		PRODUCT SPEC 製品規格	SIZE	
MATERIAL 材料				APPLICATION SPEC 取付適用規格	CAGE CODE	DRAWING NO 番号
				WEIGHT	A300779	C-1981568
				CUSTOMER DRAWING	SCALE 尺度	SHEET 2 OF 2
					2:1	REV E2