


440-632

**Stainless diagonal cutting -
slim nose**Klip Grip
Feature



- For cutting soft non-ferrous wire, max. as specified, No. 25 gauge (.018 in.) and smaller soft steel wire
- Ideal for tip cutting in delicate electronic circuitry work and where small lightweight pliers are required for use by women engaged in electronic component assembly
- Precision-machined, ground flush cutting edges
- Back clearance
- Offers up to 4 times the life of regular miniature diagonal pliers
- Patented handle spring

Cat No.	UPC No.	Packed	Description	←L→		A		B		C		Max. Dia Soft non-Ferrous Wire Inch	Soft Steel Wire Inch	Shelf Pack
				Inch	mm	Inch	mm	Inch	mm	Inch	mm			
113CG	037103489784	Boxed	Flush Cut	4 1/2	114	3/8	9	13/32	12	7/32	6	.065	.018	6
113CGV	037103489791	Carded	Flush Cut	4 1/2	114	3/8	9	13/32	12	7/32	6	.065	.018	6
115CG	037103489821	Boxed	Flush Cut	5	127	1/2	13	1/2	3	7/32	6	.083	.018	6
115CGV	037103489838	Carded	Flush Cut	5	127	1/2	13	1/2	3	7/32	6	.083	.018	6
117CG	037103489999	Boxed	Flush Cut	4	100	5/16	8	15/32	12	7/32	6	.051	.018	6
117CGV	037103490001	Carded	Flush Cut	4	100	5/16	8	15/32	12	7/32	6	.051	.018	6

Xcelite®

57CG

- Standard pliers
- For firm gripping and looping of wire
- Fine serrated jaw and coil spring
- Forged alloy steel construction, precision machining and scientific proportioning
- Red plastic-coated cushion grip provides maximum leverage



Cat No.	UPC No.	Packed	←L→		A		B		C		E		Pack wt oz	Shelf Pack
			Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm		
57CG	037103481641	Boxed	5 11/16	144	--	--	15/32	12	1/4	6	1/16	1.5	20.8	590 6
57CGV	037103481658	Carded	5 11/16	144	--	--	15/32	12	1/4	6	1/16	1.5	20.8	590 6