




FEATURES:

- Converts Bantam (Miniature Phone Plug) Female into Alligator Clips
- Shielded cable to reduce noise
- Bantam molded to the cable for optimum durability

MATERIALS:

Conn: 1st end: Miniature 3 Cond. Phone Plug. (5026 brass, 5026N nickel plated brass).

Insulation: PVC, black. Sleeve, no connection

Cable: Two cond. Shielded, 22 AWG, 7 x 30 t.c., 4.6 (.180) O.D., Y-mold insulation, PVC, gray

Conn: 2nd end: Alligator clips. Steel, nickel plated. Vinyl boots, one Black and one Red.

RATINGS:

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: 150 VRMS/DC

Current: 5 Amperes

ORDERING INFORMATION: Model 5026-XX

XX=Cable Length, Standard Lengths: 36" (914), 60" (1524), 84" (2134)

Ordering Example: 5026-84, Cable length is 84" with brass Bantam connector

5026N-60, Cable length is 60" with nickel plated brass Bantam connector

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90613 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com