

Search within category

GO

HB1B1F0BA08W1



The 20A, 208V horizontal power strip in black has four IEC C-13 and four IEC C-19 receptacles. It features a red LED current monitor and a 10' (3m) power cord with a NEMA L6-20P twist-lock plug. It is UL and c-UL listed and measures 1.7H x 17.0W x 1.85D (43mm x 431mm x 47mm). It is sold individually.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Rack PDU Type	Basic Rack PDU with Local Meter			
Monitoring	Local Meter			
Remote Outlet Switching	No			
Mount Orientation	Horizontal			
Current Rating (Amps)	20A			
Input Voltage	208V - Single Phase			
Plug Type	NEMA L6-20P			
Output Voltage	208V			
Receptacle Type	IEC C-13 and IEC C-19			
Total Number of Outlets	8			
Depth (In.)	1.85			
Depth (mm)	47.0			
Height (In.)	1.72			
Height (mm)	43.7			
Width (In.)	17.00			
Width (mm)	431.8			
Tool-Less Button Spacing (In.)	NA			
Tool-Less Button Spacing (mm)	NA			
No. of Rack Spaces	1			
Surge Suppression	No			
Amps	20A			
Cable Length	3			
Length (In.)	22.00			
UL Recognized	Yes			
Voltage	208V			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			