


NOTES:

1. TERMINAL TO BE USED IN HOUSINGS 70066-**** AND 70450-****
2. REFER TO PRODUCT SPECIFICATION PS-71851
3. REFER TO MOLEX OPERATIONS AND SERVICE MANUAL FOR CRIMP DETAILS
4. TERMINAL TO BE USED WITH (.064)/.025 SQUARE PINS
5. TERMINAL TO BE USED WITH 22-24 AWG STRANDED WIRE WITH (.163)/.064 MAX. DIA. INSULATION
6. TERMINALS SUPPLIED LOOSE PER DRAWING PK-70873-0822

PLATING:

.000030 MINIMUM GOLD PLATE IN SELECT AREA WITH .000075 MINIMUM TIN PLATE IN SELECT AREA OVER NICKEL PLATE OVERALL

*THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD.



		C1	REVISED PER ECR #U70928 MCCRATH 97/06/26		DIMENSIONS SHOWN (METRIC) INCH		REVISE ONLY ON CAD SYSTEM			
			UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°							
D	LEAD FREE UCP2004-1769 RWHITE 04/04/06	C	REVISE PER ECR# U82219 11-07-88 MMJ/MCB	INCH METRIC						
C2	REVISED ECR #U80270 MCCRATH 97/07/31	B	REVISE PER ECR #U80064 3/25/88 MMJ	3 PLACE	± .010	---				
LTR.	REVISIONS	LTR.	REVISIONS	2 PLACE	± .014	± 0.25				
				1 PLACE	---	± .35				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
DRWG.	MMJ	CHK'D.	MMJ							
PART NO.	016-02-1115	DRWG. NO.	SD-71851-0226	FILE NAME	S71851X8	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	DIV.	SIZE		
				APP'D.	WAZ	SCALE	10:1	DA B		