

Product Description

Permanent and secure sealing for areas with risks of explosion; Easy to assemble; High degree of protection



Application range

- SKINTOP® SDV-M is used together with SKINTOP® MS-M ATEX, MS-M ATEX BRUSH or SKINTOP® K-M ATEX plus (blue).
- Equipment group II / Category 2G+1D

Benefits

- Permanent and secure sealing for areas with risks of explosion
- Easy to assemble
- High degree of protection

Note

- Outside areas with a risk of explosion, also suitable for use in combination with SKINTOP® ST-M and SKINTOP® MS-M

Technical Data

Caution

Refer to the instruction leaflet for the installation dimensions and torques

Material

CR

Protection rating

IP 68 - sizes M12, M16, M20, M25, M32 IP 66 - sizes M40, M50, M63

Temperature range

-30°C to +70°C Short-term: up to +90°C

Article List

Part number	Article designation / size	Outer Ø (mm)/ from - to	Visible height (mm)	Pieces / PU
SKINTOP® SDV-M ATEX				
54113002	12 ATEX	-	SDV-M ATEX 3	50
54113012	16 ATEX	-	SDV-M ATEX 3	50
54113022	20 ATEX	-	SDV-M ATEX 3,5	50
54113032	25 ATEX	-	SDV-M ATEX 3,5	50
54113042	32 ATEX	-	SDV-M ATEX 4	25
54113052	40 ATEX	-	SDV-M ATEX 4	25
54113062	50 ATEX	-	SDV-M ATEX 4,5	10
54113072	63 ATEX	-	SDV-M ATEX 4,5	5

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.